

ARP-1314

Powerful 13,500 BTU Portable Air Conditioner with 3-Way operation can be used to cool a room, to circulate air in fan mode, and as a dehumidifier to remove moisture. Durable design provides quick and efficient cooling with a unique self-evaporating system.

Royal Sovereign Advantages

- 13,500 BTU
- Powerful Cool a room up to 600 square feet
- 3 in 1 Operation Cools, Circulates air, and dehumidifies
- 24 hour timer and Sleep Mode for energy efficiency
- Removable and washable air filter ensures high air quality
- 1 year manufacturer limited warranty, 5 years on the compressor



Royal Sovereign offers high quality, economically priced portable air conditioners specifically designed for efficient cooling and ease of use. The ARP-1314 is a 3-in-1 air comfort system with a rugged durable design. This robust air conditioner also can be used in fan mode to circulate air and as a dehumidifier removing up to 72 pints a day without emptying a bucket. Fully featured the ARP-1314 has a digital display, a fully adjustable thermostat, sleep mode, 24 hour timer, variable speed fan controls, and a remote control. Built-in casters and easy set-up (window ventilation kit included) allows this Portable Air Conditioner to be easily moved from room-to-room.

AFFORDABLE

USER FRIENDLY

RELIABLE



ARP-1314

SPECIFICATIONS

MODEL	ARP-1314
BTU Cooling	13,500
BTU Heating	No
Room Size (Sq. Ft)	550 - 700
Dual/ Single Hose	Single
Digital or Analog Controls	DIGITAL
Thermostat Range (degrees F)	62° - 88°
Timer	24 HRS
Sleep Mode	YES
Auto Restart	YES
Remote Control	YES
Adjustable Louvers	YES
Oscillating Mode	YES
# Fan Speeds	3
Fan only mode	YES
Airflow Volume (Cubic Feet/ Minute)	317
Water Removal System	Self Evaporating
Dehumidifying Capacity (# pints/ Day)	72
Washable Filter (Yes/ No)	YES
Window Kit Included	YES
Hose Length (Ft)	5
Size of Window accommodated (Min/ Max in.)	2.75 - 4.13
UPC Code	8 49023 05009 4
Unit Dimensions (inches)	19.3 X 31.9 X 15.7
Net weight (PAC only w/o window kit & hose)	75 lbs.
Package Dimensions (inches)	23.4 X 36.2 X 25.4
Unit packaging weight	92.6 lbs.
Pallet Quantity	8
40' Container Quantity	176
Coolant Type	R410A
Power Supply (V/Hz)	115V/60Hz
Noise Level DB (Low Fan)	53
Power Consumption (Watts)	1480
Current	11.9A
EER	9.5



Your Local Dealer:

