

RDH-130K

30 Pint Dehumidifier

Provide efficient dehumidification power for healthier air quality and a drier, more comfortable environment



Energy Efficient

Removes the same amount of moisture as a similarly-sized conventional units, but use up to 15% less energy

Eco Friendly Refrigerant

Non ozone depleting R134A or R410A refrigerant depending on model capacity

Washable Filter

Collects large dust particles and prevents bacteria build up. Easy to remove for cleaning

Digital Controls

Digital display and electronic controls allows you to set the desired humidity level, fan speed and 24 hour timer

Auto Defrost

Prevents ice build up on the condensing coils

Auto Restart

Restarts after a power outage at previous settings

Affordable

**User
Friendly**

**Energy
Star
Rated**



30 Pint Dehumidifier

Digital Controls




Washable Filter

Washable air filter prevent bacteria and mold growth



Rolling Casters



FEATURES

Type:	Bucket
Fan Speeds:	2
Dehumidifying Capacity:	30 Pints/Day
Humidistat:	Adjustable
Continuous Direct Drain Option:	Yes
Energy Star Rated:	Yes
Digital Display:	Yes
Washable Filter:	Yes
On/Off Timer:	Yes
Auto Restart:	Yes
Auto Defrost:	Yes
Refrigerant:	R134A
Noise Level:	52dB/49dB
Safety Certification:	cETL

ELECTRICAL RATING

Voltage:	115V/60Hz
Consumption:	420 W

DIMENSIONS

Unit (W x D x H):	14.1" x 10.5" x 19.9"
Unit Weight:	29.8 lbs.
Individual/Master Carton (W x D x H):	15.7" x 12.4" x 21.0"
Individual/Master Carton Weight:	33.1 lbs.
Carton Count = 1	

Country of Origin:	China
--------------------	-------

UPC CODE

Individual/Master Carton:	0 35565 85009 8
---------------------------	-----------------

WARRANTY

1 Year