



CSP300WUR1 | PROFESSIONAL SURGE PROTECTOR

Protect home and office computers, electronics, and home theater equipment

The Professional Surge Protector CSP300WUR1 safeguards common home and office devices, such as computers and electronics, by absorbing spikes in energy caused by storms and electrical power surges. Designed for convenience, the portable CSP300WUR1 is ideal for travelers. It provides 600 joules of protection, has three surge-protected outlets, and a wall-tap plug. Two USB ports (2.1 Amp shared) charge personal electronics, including smartphones, digital cameras, MP3 players, and other devices.

The CSP300WUR1 also features metal oxide varistor (MOV) technology, an EMI/RFI noise filter, a status indicator, and impact-resistant casing. This surge suppressor comes with a 1-Year Limited Warranty and a Connected Equipment Guarantee.



TYPICAL APPLICATIONS

- Mobile Devices
- Personal Electronics
- Cell Phones
- Personal Computers

FEATURES

- Surge suppression: 600 J
- Volts: 125 V
- Plug type: Wall Tap
- Outlet type: 3 NEMA 5-15R (surge-protected)
- USB charge ports: 2
- Communication: USB
- EMI/RFI Filtration: Yes
- LED indicator: Yes
- Warranty: 1-Year Limited
- Connected Equipment Guarantee: \$50,000

SPECIFICATIONS

INPUT

Circuit Breaker	None
Cord Length	Wall-tap
Input Plug Type	NEMA 5-15P
Maximum Input Current	15 A
Plug Style	Wall-tap

OUTPUT

Outlet Type	3 - NEMA 5-15R
Outlets - Total	3
USB Charge Port	Yes
USB Charge Port Amperage	2.1 A (Shared)
USB Charge Port Quantity	2
USB Charge Port Type	Type A
USB Charge Port Voltage	5 VDC

SURGE PROTECTION & FILTERING

Attenuation	32 dB
Clamping Voltage	400V (H-N, H-G)
Coax Protection RG6	None
EMI/RFI Filtration	150 KHz 100 MHz Yes
Maximum Surge Current	30,000 A
Maximum Surge Current H-G	15,000 A
Maximum Surge Current H-N	15,000 A
Maximum Surge Current N-G	N/A
Maximum Surge Voltage	6,000 V
Response Time	<1 Nanosecond
Surge Suppression (Joules)	300 J

CSP300WUR1

PROFESSIONAL SURGE PROTECTOR

SPECIFICATIONS CONT.

PHYSICAL

Color	White
Form Factors Supported	Direct Plug
Material of Construction	Plastic

PHYSICAL DIMENSIONS

Physical Dimensions - WxHxD (cm)	9.14 x 12.19 x 3.23 cm
Physical Dimensions - WxHxD (mm)	91 x 122 x 32 mm
Physical Dimensions - WxHxD (in.)	3.6 x 4.8 x 1.27 in.
Weight (kg)	0.19 kg
Weight (lb)	0.42 lbs.

SHIPPING DIMENSIONS

Shipping Dimensions - WxHxD (cm)	15.88 x 5.97 x 9.63 cm
Shipping Dimensions - WxHxD (mm)	158.75 x 59.69 x 96.27 mm
Shipping Dimensions - WxHxD (in.)	6.25 x 2.35 x 3.79 in.
Weight (kg)	0.23 kg
Weight (lb)	0.50 lbs.

CERTIFICATIONS

Environmental	RoHS Compliant
Safety	UL1449 3rd Edition

WARRANTY

CEG Amount	\$50,000
Connected Equipment Guarantee	Lifetime
Product Warranty	1-Year Limited Warranty