



# CSP604U PROFESSIONAL SURGE PROTECTOR

Protect home and office computers, electronics, and home theater equipment

The Professional Surge Protector CSP604U from CyberPower offers vital surge suppression for common home and office devices such as computers and electronics. It prevents spikes in energy caused by storms and electrical power surges and is ideal for safeguarding personal computers, phones/faxes/modems, and other consumer electronics. The CSP604U provides 1,200 joules of protection and six surge-protected outlets. Its two USB charge ports (2.4 Amp shared) keep tablets, smartphones, and other rechargeable electronics ready to use. The 4 ft. power cord has a right-angle plug with a 45-degree offset.

Features of the CSP604U include automatic shutdown, metal oxide varistor (MOV) technology, and an EMI/RFI noise filter. It also has an LED indicator (Protected), keyhole mounting slots, and impact-resistant casing. The CSP604U comes with a 1-Year Limited Warranty and a \$50,000 Connected Equipment Guarantee.

## TYPICAL APPLICATIONS

- Mobile Devices
- Personal Electronics
- Cell Phones
- Personal Computers

## FEATURES

- Surge suppression: 1,200 J
- Volts: 125 V
- Circuit breaker: 15 A
- Plug type: NEMA 5-15P (45° off-set)
- Outlet type: 6 NEMA 5-15R (surge-protected)
- Power cord: 4 ft
- USB charge ports: 2
- LED indicator: Yes
- Keyhole slots: Yes
- EMI/RFI Filtration: Yes
- Warranty: 1-Year Limited
- Connected Equipment Guarantee: \$50,000



## SPECIFICATIONS

INPUT		SURGE PROTECTION & FILTERING	
Circuit Breaker	15 A	Attenuation	43 dB
Cord Length	4 ft (1.2 m)	Clamping Voltage	400V (H-N, H-G, N-G)
Input Plug Type	NEMA 5-15P	Coax Protection RG6	None
Maximum Input Current	15 A	EMI/RFI Filtration	150 KHz 100 MHz Yes
Plug Style	Right Angle - 45° Offset	Maximum Surge Current	60,000 A
OUTPUT		Maximum Surge Current H-G	15,000 A
Outlet Type	6 - NEMA 5-15R	Maximum Surge Current H-N	30,000 A
Outlets - Total	6	Maximum Surge Current N-G	15,000 A
USB Charge Port	Yes	Maximum Surge Voltage	6,000 V
USB Charge Port Amperage	2.4 A (Shared)	Response Time	<1 Nanosecond
USB Charge Port Quantity	2	Surge Suppression (Joules)	1,200 J
USB Charge Port Standard	Type A		
USB Charge Port Type	2 Type A		
USB Charge Port Voltage	5 VDC		

# CSP604U

## PROFESSIONAL SURGE PROTECTOR

### SPECIFICATIONS CONT.

PHYSICAL		CERTIFICATIONS	
Color	Black	Environmental	RoHS Compliant
Form Factors Supported	Keyhole (Wall Mount or Under-counter Installation)	Safety	UL 1363
Keyhole Mounting Slots	Yes	WARRANTY	
Material of Construction	Plastic	CEG Amount	\$50,000
PHYSICAL DIMENSIONS		Connected Equipment Guarantee	Lifetime
Physical Dimensions - WxHxD (cm)	5.59 x 3.78 x 29.46 cm	Product Warranty	1-Year Limited Warranty
Physical Dimensions - WxHxD (mm)	56 x 38 x 295 mm		
Physical Dimensions - WxHxD (in.)	2.2 x 1.49 x 11.6 in.		
Weight (kg)	0.47 kg		
Weight (lb)	1.03 lbs.		
SHIPPING DIMENSIONS			
Shipping Dimensions - WxHxD (cm)	34.62 x 4.62 x 10.67 cm		
Shipping Dimensions - WxHxD (mm)	346.2 x 46.23 x 106.68 mm		
Shipping Dimensions - WxHxD (in.)	13.63 x 1.82 x 4.2 in.		
Weight (kg)	0.56 kg		
Weight (lb)	1.23 lbs.		