

SunBriteTV®

True Outdoor Television

MODEL SB-4670HD

DISPLAY

AVAILABLE COLORS



White



Silver



Black



SHOWN IN BLACK

KEY FEATURES

- 46" Signature Series True Outdoor LED Television for permanent outdoor installation.
- 46-inch Diagonal Active Matrix TFT LED.
- Powder-coated aluminum exterior designed to protect internal components from rain, dust, insects, humidity, and salt air.
- Multi-fan airflow system keeps the unit cool and dry in temperatures up to 122 degrees F.
- Ability to operate in cold weather (-24 degrees F).
- RS232 serial control with discrete on, off, and input control (located in the cable-entry compartment).
- Rear IR receiver (located in the cable-entry compartment).
- Innovative water-tight Cable Entry System seals out moisture and allows for easy hook-ups.
- Weatherproof built-in 20W speakers.
- Weatherproof remote control.
- Weatherproof control buttons.
- Remote Control Lock-Out prevents unauthorized users from changing the programming.

| | | |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SCREEN | SCREEN 46-inch Diagonal Active Matrix TFT LED RESOLUTION 1920 x 1080 Full-HD 1080p ASPECT RATIO 16:9 CONTRAST RATIO 4000:1 | FRAME RATE 60 Hz VIEWING ANGLE 178° x 178° RESPONSE TIME 6.5 milliseconds TV FORMATS 1080p, 1080i, 720p, 720i, 480p, 480i |
| CONNECTIONS | RF Antenna/CATV (ATSC/QAM/NTSC) x1 HDMI HDMI™ Input x2 VIDEO COMPOSITE S-Video x1 and Composite Video x1, L/R Audio Inputs x1 VIDEO COMPONENT YPbPr plus Stereo Audio x2 PC 15-pin D-sub VGA plus Stereo Audio | CONTROL SET RS232 Serial, Discrete IR Control, Concealed IR Window AUDIO OUT SPDIF Audio, Analog 1/8" headphone jack SPEAKERS 20 WATT built-in speakers INPUT POWER 100-240 VAC, 50-60 Hz 2.8 A Max (80 WATTS/.7a@120v) |
| TEMPERATURE TOLERANCES | OPERATING TEMP -24° to 122° F. (-31° to 50°C.) NON-OP. TEMP -24° to 140° F. (-31° to 60°C.) (OFF MODE WITH POWER APPLIED) The non-operating temperature feature requires power to be applied. | |
| PHYSICAL SPECS | ACCESSORIES INCLUDED Weatherproof remote control, outdoor dust cover. EXTERIOR Powder-coated aluminum. EXTERIOR COLORS Black, Silver, White TV DIMENSIONS 42.41in W x 25in H x 3.74in D TV WEIGHT 48.0 lbs. | SHIPPING DIMENSIONS 47.5in L x 9in W x 33in H SHIPPING WEIGHT 67.0 lbs. RESIDENTIAL WARRANTY Two-year parts and labor. COMMERCIAL WARRANTY Two-year parts and labor. |