

Vuelta

ra newheights™

Crank Height Adjustable Table

Contemporary Style

Our unique shape offers a clean, edgy look with an attractive anodized finish, only available by using extruded aluminum.

Durable Design

Our most affordable height adjustable table that offers true sit-to-stand travel of 27" - 47".

Built to Last

Manufactured in the USA with a commitment to quality, long term reliability and environment friendly.



Vuelta

GSA

MADE IN THE
USA

Vuelta Features

- Height Range: 27"- 47" H.
- Lifting Capacity Base Only: 125 pounds per column.
- Height Adjustment: six turns per inch.
- Mounting clearance (depth) for under desk accessories (note: any length track system can be mounted on an angle):
24" workstation is 14"
30" workstation is 17"
- Available with worksurface or base only.
- Bases available for 24" and 30" deep worksurfaces.
- Custom size worksurfaces available.

See Spec Book for complete specifications: raproducts.com/price



Hideaway Handle May be Mounted Left or Right Standard is Right Side

Legs available with 3" soft caster foot.



Ideal Applications:

- Call Centers
- Schools
- Hospitals
- Libraries
- Office Space

Finishes

Laminate Surface Colors

3mm matching edge banding except Chocolate Flame and Gray Matrix, which have black edge banding



Pearwood
(P)



Hardrock Maple
(HM)



Natural Oak
(NO)



Cherry (C)



Mahogany
(M)



Chocolate Flame
(CF)



Gray Matrix
(GM)



Black
(B)



Galaxy White
(GW)

Base Colors



Black



Silver




Finish Options

(Only Available on Standard 24" Configurations)



Black Base
Cherry Top (BC)



Silver Base
Cherry Top (SC)


Black Base
Hardrock Maple
Top (BHM)



Silver Base
Hardrock Maple
Top (SHM)

High-pressure laminate and custom colors available

You may also like...



Swivel Pencil Tray
300PTB



Myriad™ with FastAction
Precision Arm MFP21



310CPU
Adjustable CPU Holder



CT3000 Task Chair



Hover Series 2
Monitor Arm HS3111



GSA #GS-28F-0035M

Code #NH0314 • ©2014 RightAngle Products • 800.298.4351 • raproducts.com