



## Mini DisplayPort Dongle Adapters

- Adapts a Mini DisplayPort Source device to VGA, DVI or HDMI compatible displays
- Supports DisplayPort 1.2 specification
- Lifetime Warranty

# Specifications: Mini DisplayPort Dongle Adapters

## Electrical Specifications:

---

Voltage Rating:	30v
Conductor Resistance:	@ 20°C max
Insulation Resistance:	10MΩ/km
Time Delay:	5.2ns/m (max)
Attenuation:	5.02dB@100-450MHz    7.69dB@1GHz
	12.595dB@2GHz    17.495dB@3GHz
	22.395dB@4GHz    27.295dB@5GHz
	32.195dB@6GHz    37.095dB@7GHz

## Physical Specifications:

---

Operating Temperature:	0°C to 50°C
Storage Temperature:	-25°C to 70°C
Approvals:	CE
Warranty:	Lifetime

### Conductor (2 Conductor, 5 Pair):

---

Conductor:	32AWG (7/0.08TC)
Insulation:	FM-PE, ID:0.63±0.05mm
Color:	White/Brown, White/Red, White/Orange, White/Green White/Blue
Drain:	32AWG (7/0.08TC) HD-PE ID:0.63±0.05
Shield:	AL-Mylar Wrap Coverage—100%

### Conductor (5 Conductors):

---

Conductor:	32AWG (7/0.08TC)
Insulation:	HD-PE, ID:0.5±0.05mm
Color:	Red/Orange/Yellow/Green/ White





## Overall Cable

---

Jacket:	PVC
Shield:	AL-Mylar—Coverage 100% Braid—16/9/0.12
Drain:	2:30AWG (7/0.08 BC)
OD:	5.2±0.2



# Specifications: Mini DisplayPort Dongle Adapters



Part Number	Description	Weight (lbs)
54311	8in Mini DisplayPort Male to Single Link DVI-D Female Adapter Converter—Black	0.094
54312	8in Mini DisplayPort Male to Single Link DVI-D Female Adapter Converter—White	0.094
54313	8in Mini DisplayPort Male to HDMI Female Adapter Converter—Black	0.093
54314	8in Mini DisplayPort Male to HDMI Female Adapter Converter—White	0.093
54315	8in Mini DisplayPort Male to VGA Female Adapter Converter—Black	0.095
54316	8in Mini DisplayPort Male to VGA Female Adapter Converter—White	0.095

