

WorkForce® WF-2630

WIRELESS | PRINT | COPY | SCAN | FAX



All-in-One

WorkForce

Easy wireless¹ printing from this compact, productive all-in-one.

Fast printing — professional-quality prints at speeds of 9 ISO ppm (black) and 4.7 ISO ppm (color)[†]

Wireless and Wi-Fi Direct^{®1} — easily print from iPad[®], iPhone[®], tablets and smartphones²

Affordable individual ink cartridges — replace only the color you need

Smallest footprint in its class³ — save space in your home office

Do more — 100-sheet paper capacity; plus a 30-page Auto Document Feeder

Documents that last — smudge, fade and water resistant prints

Sharp documents — professional-quality black text delivers crisp, high-quality proposals, reports and brochures

Increase productivity — print, copy, scan and fax; plus scan to the cloud⁴

Reliable — designed to be jam free⁵

PC-Fax — fax documents directly to/from your computer

Print

Printing Technology 4-color (CMYK) drop-on-demand MicroPiezo® inkjet technology

Printer Language Epson ESC/P®-R

Maximum Print Resolution 5760 x 1440 optimized dpi

ISO Print Speed† Black 9.0 ISO ppm / Color 4.7 ISO ppm

Minimum Ink Droplet Size 3 droplet sizes, as small as 3.0 picoliters

Duty Cycle‡ Up to 3000 pages (Recommended monthly page volume up to 600 pages)

Copy

ISO Copy Speed†† Black 8 ISO cpm / Color 3.8 ISO cpm

Copy Quality Color/Black-and-white: Standard/Best

Copy Quantity 1 – 99 (PC-free)

Maximum Copy Size 8.5" x 14"

Copy Features Fit to Page, Resize, Adjustable Copy Density, Borderless

Scan

Scanner Type Color flatbed/ADF

Photoelectric Device Color CIS line sensor

Maximum Hardware Resolution 2400 dpi

Hardware Resolution 1200 x 2400 dpi

Maximum Resolution 9600 dpi interpolated

Scanner Bit Depth 48-bit color input / 24-bit color output

Scan Features Scan to PC, Scan to Cloud* (including email)

Fax

Fax Specifications

Black-and-white and color

Modem: 33.6 Kbps — as fast as 3 sec per page

Memory: Up to 100 pages

Speed dials: 60 (max.)

PC-Fax

Connectivity

Standard Connectivity

Hi-Speed USB

Wireless (802.11 b/g/n)†

Wi-Fi Direct†

Operating Systems Windows® 8.x (32-bit, 64-bit), Windows 7 (32-bit, 64-bit), Windows Vista® (32-bit, 64-bit), Windows XP® SP3 (32-bit), Windows XP Professional x64 Edition, Windows Server® 2012 R2†, Windows Server 2012†, Windows Server 2008 R2†, Windows Server 2008†, Windows Server 2003 R2†, Windows Server 2003†, Mac OS® X 10.5.8 – 10.9.x‡

Mobile Printing

Epson Connect™‡ Epson® Email Print, Epson iPrint™ Mobile App, Epson Remote Print

Other Kindle Fire™, Apple® AirPrint™, Google Cloud Print™

Paper Handling

PC-free Paper Support Plain (Letter, Legal, A4), (8" x 10", 5" x 7", 4" x 6")

Maximum Paper Size 8.5" x 47.2"

Paper Sizes 3.5" x 5", 4" x 6", 5" x 7", 8" x 10", 8.5" x 11", 8.5" x 14", A4, A6, half letter, executive, user definable (3.5" – 47.2" in length)

Borderless Photo Sizes 4" x 6", 5" x 7", 8" x 10", 8.5" x 11", A4

Paper Types Plain paper, Epson Bright White Paper, Epson Presentation Paper Matte, Epson Premium Presentation Paper Matte, Epson Premium Presentation Paper Matte Double-sided, Epson Premium Photo Paper Glossy, Epson Ultra Premium Photo Paper Glossy, Epson Premium Photo Paper Semi-gloss

Envelope Types No. 10; plain paper, bond paper, air mail

Input Paper Capacity

100 sheets plain paper

10 envelopes, 20 sheets photo paper

Auto Document Feeder 30 sheets

General

Display 2.2" mono graphic LCD

Temperature

Operating: 50 ° to 95 °F (10 ° to 35 °C)

Storage: -4 ° to 104 °F (-20 ° to 40 °C)

Relative Humidity

Operating: 20 – 80% RH

Storage: 5 – 85% RH (no condensation)

Sound Level

Power: 5.7 B(A)

Pressure: 43 dB(A)

Rated Voltage AC 100-240V Universal (Automatic)

General (continued)

Rated Frequency 50 – 60 Hz

Rated Current 0.5A – 0.3A

Power Consumption

Approx. 11 W ISO 24712 (Standalone copy printing)

Approx. 4.0 W (Standby)

Approx. 1.7 W (Sleep)

Approx. 0.3 W (Power off) ENERGY STAR® qualified

Safety Approvals

Safety standards UL60950, CSA C22.2 No. 60950

EMI FCC Part 15 subpart B class B,

CAN/CSA-CE/IEC CISPR 22 class B

Telecom Regulations FCC Part 68 (U.S.A.), IC/CS03 (Canada)

Country of Origin Indonesia

Weight and Dimensions (W x D x H)

Printing: 15.4" x 21.3" x 11.5"

Storage: 15.4" x 14.8" x 8.7"

Weight: 12.8 lb

What's in the Box Epson WorkForce WF-2630 all-in-one, instruction manual, CD-ROM for product setup, power cord, DURABrite® Ultra Ink cartridges* – Four 220-series ink cartridges: Black, Cyan, Magenta, Yellow

Software Included‡ Epson printer driver, Epson Scan, PC-Fax

Warranty One-year limited warranty in the U.S. and Canada

Ink

Ink Type DURABrite Ultra pigment ink (smudge, fade and water resistant)

Ink Palette Cyan, Magenta, Yellow and Black

Ink Cartridge Configuration Four individual ink cartridges

Fade Resistance / Print Longevity†† Up to 118 years

Replacement Ink Cartridges

220 Standard-capacity Black, Cyan, Magenta, Yellow (Yields, ISO pages – Black: 175, Color: 165)

220XL High-capacity Black, Cyan, Magenta, Yellow (Yields, ISO pages – Black: 500, Color: 450)

Printer is designed for use with Epson cartridges only, not third-party cartridges or ink. www.epson.com/cartridgeinfo

Eco Features

Uses up to 70% less power than laser printers¹²

RoHS compliant

Recyclable product¹³

Epson America, Inc. is a SmartWaySM Transport Partner¹⁴

Ordering Information

Product Name

WorkForce WF-2630

Product Code

C11CE36201

*This product uses only genuine Epson-brand cartridges. Other brands of ink cartridges and ink supplies are not compatible and, even if described as compatible, may not function properly.

† Black and color print speeds are measured in accordance with ISO/IEC 24734. Actual print times will vary based on system configuration, software, and page complexity. For more information, visit www.epson.com/printspeed | †† Black and color copy speeds are determined in accordance with ISO/IEC 29183. Actual copy times will vary based on system configuration and page complexity. For more information, visit www.epson.com/copyspeed | † Wi-Fi CERTIFIED™; level of performance subject to the range of the router being used. Wi-Fi Direct may require printer software. | ‡ Most features require an Internet connection to the printer, as well as an Internet- and/or email-enabled device. For a list of Epson Connect enabled printers and compatible devices and apps, visit www.epson.com/connect | ‡ Smallest footprint among inkjet all-in-ones (print, copy, scan and fax) priced at \$99 (USD) or less as of January 2014. | ‡ Scan to cloud requires an Internet connection, a free Epson Connect account and a destination email address or cloud storage account. For a list of supported cloud services, visit www.epson.com/connect | ‡ Performance will vary based on print task and use conditions. | ‡ Monthly duty cycle is the highest duty a user could expect in a month, based on near-constant operation of a device of this kind. It is not recommended that the device be run at this duty. For best device performance, run the device at the recommended duty. | ‡ Only printing and scanning are supported under Windows Server OS. | ‡ Some applications and/or functions may not be supported under Mac OS X. | ‡ Replacement cartridge yields are based on ISO/IEC 24711 tests in default mode printing continuously. Cartridge yields vary considerably for reasons including images printed, print settings and humidity. Yields may be lower when printing infrequently or predominantly with one ink color. All ink colors are used for printing and all-in-one maintenance, and all colors have to be installed for printing. For print quality, part of the ink from the included cartridges is used for printer startup and a variable amount of ink remains in the cartridges after the "replace cartridge" signal. For details, see www.epson.com/cartridgeinfo | ‡ Internet access is required to install OS X drivers and software. | ‡ Display permanence based on accelerated testing of prints displayed under glass in indoor display conditions; album permanence based on accelerated testing of prints in dark storage conditions. Actual print stability will vary according to media, printed image, display conditions, light intensity, temperature, humidity and atmospheric conditions. Epson does not guarantee the longevity of prints. For maximum print life, display all prints under glass or UV filter or properly store them. | ‡ Compared to best-selling, color multifunction laser printers priced at \$499 (USD) or less, as of March 2014. Actual power savings will vary by product model and usage. | ‡ For convenient and reasonable recycling options, visit www.epson.com/recycle | ‡ SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

Specifications are subject to change without notice. EPSON, DURABrite, Epson ESC/P, MicroPiezo and WorkForce are registered trademarks. EPSON Exceed Your Vision is a registered logomark and Epson Connect and Epson iPrint are trademarks of Seiko Epson Corporation. Built to Perform is a trademark of Epson America, Inc. Apple, iPad, iPhone and Mac OS are trademarks of Apple Inc., registered in the U.S. and other countries. AirPrint is a trademark of Apple Inc. Google Cloud Print is a trademark of Google Inc. Wi-Fi Direct is a registered trademark and Wi-Fi CERTIFIED is a trademark of the Wi-Fi Alliance. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2014 Epson America, Inc. CPD-41107 6/14