

# Standalone 1:5 USB Flash Drive Duplicator and Eraser – Flash Drive Copier

Product ID: USBDUP15



The USBDUP15 OnetoFive USB flash drive duplicator and eraser lets you quickly clone up to five backups of a single USB flash drive, or securely erase up to five flash drives, without connecting to a host computer.

## Maximum Portability

Featuring a compact lightweight design that you can carry anywhere, and standalone operation that does not require a host computer, the flash drive duplicator and eraser has a small desktop footprint and is great for travel. Perfect for software and marketing content distribution in the office or on-the-go.

## Hassle-free Operation

With an easy-to-read LCD display and intuitive four button menu operation, the USBDUP15 ensures hassle-free setup and control. The menu gives you push-button access to many value-added features that ensure simple task management such as: Capacity & Speed Check, Copy & Compare, Asynchronous Copy, and many more. It also provides numerous advanced setup options for experienced users.

## Fast Duplication and Secure Erasing

This versatile device is both hard drive cloner and eraser in one, and offers two duplication modes (File & System Copy / Whole Copy) with up to 1.5GB/m at Whole Copy mode. It offers three erase modes (Quick Erase / Full Erase / DoD Erase) giving you the freedom to choose the best solution for your application.

The USBDUP15 is TAA compliant and backed by a 2-year StarTech.com warranty and lifetime technical support.

**Note: The USBDUP15 flash drive duplicator supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a hard drive docking station or USB enclosure (sold separately)**

### Certifications, Reports and Compatibility



### Applications

- Software and operating system updating and distributions
- Marketing collateral copying and distribution
- Rich media copying and distributions
- Quickly backup USB flash drives without a host computer
- Create exact copies of a USB flash drive in law enforcement and forensic investigations
- Thoroughly erase data from a flash drive, for added data security and peace of mind
- Clean and prepare USB drives for reuse
- Testing and evaluating USB drives

### Features

- Supports USB 3.0/2.0/1.1 flash drives
- 1:5 standalone duplication with 2 duplication modes
- Erase up to 5 USB flash drives with single-pass and multi-pass overwriting/DoD erasing
- High-speed duplication at up to 1.5GB per minute
- Compact, lightweight design
- TAA compliant
- Built-in LCD display
- Check drive capacity, quality and speed with intuitive task management
- Supports both Asynchronous and Synchronous copy modes, for quick batch swapping with 64 MB of internal memory

<b>Hardware</b>	Warranty	2 Years
	Buffer Size	64 MB
	Bus Type	USB 2.0
	Compatible Drive Types	USB Flash Drive
	Drive Installation	Removable
	Number of Drives	6
<b>Performance</b>	Duplication Modes	System and File Sector by Sector (Whole Drive)
	Duplication Speed	1.5GBpm
	Erase Modes	Quick Erase
		1-Pass Overwrite (NIST SP 800-88 Rev 1 - Clear) 3-Pass Overwrite
<b>Connector(s)</b>	Drive Connectors	6 - USB Type-A (4 pin) USB 2.0 Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	System and Cable Requirements	For duplication, the destination drives must be of equal or greater capacity than the source drive.  Supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately) and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure (sold separately)
<b>Indicators</b>	LED Indicators	5 - Green (Activity/Successful Copy)
		5 - Red (Error)
<b>Power</b>	Center Tip Polarity	Positive
	Input Voltage	100 - 240 AC
	Output Current	2
	Output Voltage	5 DC
	Plug Type	H
	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	5% ~ 95% RH
	Operating Temperature	5°C ~ 45°C (41°F ~ 113°F)
	Storage Temperature	-20°C ~ 85°C (-4°F ~ 185°F)

<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Plastic
	Product Height	1 in [2.5 cm]
	Product Length	6.6 in [16.7 cm]
	Product Width	4.7 in [12 cm]
	Weight of Product	11.2 oz [318 g]
<b>Packaging Information</b>	Package Height	3.2 in [82 mm]
	Package Length	9.1 in [23.1 cm]
	Package Width	7.1 in [18 cm]
	Shipping (Package) Weight	26.2 oz [742 g]
<b>What's in the Box</b>	Included in Package	<p>1 - Duplicator</p> <p>1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand</p> <p>1 - Instruction Manual</p>

Product appearance and specifications are subject to change without notice.