

# valor



## Valor V 50H LG

### 50cm wide freestanding high level gas cooker



WHITE



BLACK

- **Conventional Gas Oven**  
Ideal for traditional roasting, this type of oven is hotter at the top than the bottom. You can put your meat in the middle, roast potatoes towards the top and a pudding towards the bottom. The higher temperatures at the top also make it ideal for Yorkshire puddings. You'll need to preheat the oven to get it to the right temperature before you start cooking.
- **Gas Grill**  
You can vary the grilling temperature making it ideal to cook a range of foods from toast to steak.
- **Easy Clean Enamel**  
Wipe away spills easily with our specially designed enamel which helps prevent food from sticking on to the surface.
- **Made In Britain**

# valor

## TECHNICAL SPECIFICATION

<b>Hob</b>			
Hob summary	4 gas burners		
No of burners/elements	4		
<b>Gas Hob</b>			
Burner 1 (kW)	3		
Burner 2 (kW)	2		
Burner 3 (kW)	2		
Burner 4 (kW)	1		
Gloss enamel pan supports	Yes		
Push button ignition	Yes		
<b>High Level Grill</b>			
Fuel	Gas		
Power	3.5		
<b>Cavity 1</b>			
Position	Main		
Main/second oven	Main		
Function	Conventional Oven		
Fuel	Gas		
No. of functions	1		
<b>Gas oven/grill</b>			
Conventional gas oven	Yes		
Energy rating	B		
<b>Cavity features</b>			
Actual capacity (litres)	62		
Usable capacity (litres)	43		
Cavity dimensions (HxWxD mm)	345x415x420		
Power (kW)	2.5		
Energy consumption (kWh)	1.72		
No of shelves	2		
No of shelf positions	5		
Usable area of shelves (WxD mm)	455x307		
Easy clean enamel	Yes		
Door type	Glass		
Door glazing	Double		
Viewing window	Yes		
Door opening	Side opening		
Position	Bottom		
Function	Storage		
<b>Timer</b>			
No timer	Yes		
<b>Features</b>			
Adjustable feet	Yes		
<b>Accessories (included)</b>			
<b>Removable Parts (for cleaning)</b>			
Hob burners	Yes		
Pan supports	Yes		
Pan supports	Yes		
Shelves	Yes		
<b>Installation</b>			
Gas type	Natural Gas		
Gas inlet type	1/2 BSP Female		
Gas inlet position	Rear right		
Supply voltage	220 V		
Lead length	1.9		
Total gas power load (W)	14		
Fuse size (A)	13		
Fitted 3 pin plug	Yes		
<b>Dimensions</b>			
<b>Packed</b>			
Height (mm)	1075		
Width (mm)	610		
Depth (mm)	755		
Weight (kg)	48.45		
<b>Product</b>			
Height (mm)	1412		
Width (mm)	502		
Depth (mm)	602		
Weight (kg)	46		
<b>Finish &amp; codes</b>			
Colour	White		
SKU code	444443418		
EAN code	5052263034181		
Colour	Black		
SKU code	444443419		
EAN code	5052263034198		