

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

## 10Gb Duplex Multimode 50/125 OM3 LSZH Fiber Patch Cable with Push/Pull Tab Connectors, (LC/LC) - Aqua, 3M (10 ft.)

MODEL NUMBER: **N820-03M-T**



### Features

- 3M ( 10-ft ) LC/LC, OM3 rated
- Push/Pull tab connectors offer maximum accessibility in high density installations; install / remove with one hand without needing additional tools
- Slim uniboot design saves space and makes cables easier to manage
- Premium-grade ceramic ferrule designed specifically for 10GbE and faster applications
- Sturdy plastic housing for long-lasting durability
- 10GbE speed to 300 meters @850nm
- Use with VCSEL and LED laser light sources
- High-Speed, High-Bandwidth, Low-Cost
- Backward compatible with legacy LAN's
- Ideal for Fibre Channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant

### Highlights

- Push/Pull tab connectors offer maximum accessibility in high density installations; install / remove with one hand without needing additional tools
- Slim uniboot design saves space and makes cables easier to manage
- Premium-grade ceramic ferrules designed specifically for 10GbE and faster applications
- Sturdy plastic housing for long-lasting durability
- Backward compatible with existing 50/125 fiber
- Max 10GbE distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket

### Package Includes

- 3M ( 10-ft ) Duplex Multimode 50/125 Aqua OM3 Fiber Patch Cable with Push/Pull Tabs, LC/LC

## Specifications

| OVERVIEW     |              |
|--------------|--------------|
| UPC Code     | 037332184498 |
| Technology   | Multimode    |
| Optical Mode | OM3          |



| <b>PHYSICAL</b>                      |                                     |
|--------------------------------------|-------------------------------------|
| Color                                | Aqua                                |
| Clad Diameter                        | 125 micron                          |
| Core Diameter                        | 50 micron                           |
| Number of Fibers                     | 2                                   |
| Cable Length (ft.)                   | 9.8                                 |
| Cable Length (m)                     | 3                                   |
| Cable Length (in.)                   | 118.1                               |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27                |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50                  |
| Shipping Weight (kg)                 | 0.02                                |
| Shipping Weight (lbs.)               | 0.05                                |
| <b>COMMUNICATIONS</b>                |                                     |
| Network Speed                        | 10Gbps / 40Gbps / 100Gbps           |
| <b>CONNECTIONS</b>                   |                                     |
| Side A - Connector 1                 | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| Side A - Connector 2                 | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| Side B - Connector 1                 | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| Cable Style                          | Slim                                |
| <b>SPECIAL FEATURES</b>              |                                     |
| Push/Pull Tabs                       | Yes                                 |
| <b>WARRANTY</b>                      |                                     |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty           |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.triplite.com/products/product-certification-agencies>