

IDS215

21.5" Touch Display



The IDS215 21.5" touch display is one of TouchSystems' innovative line of bezel-free, dual touch solutions, well suited to retail, self-service, gaming and entertainment applications. The display is LED back lit, ensuring crisp images and brilliant colors. The stand pivots a full 90 degrees to face directly up for added flexibility.

Specifications



Viewable Image Size	21.5"
Touch Technology	Dual Touch
Pixel Pitch	.25 mm
Brightness	220 cd/m ²
Contrast Ratio	5000:1
Aspect Ratio	16:9
Resolution	1920 x 1080 @ 60 Hz
Response Time	16 ms
Viewing Angle	178° Vertical: 178° Horizontal
Video Connectivity	DVI, VGA
Colors	16.7 million
Touch Communication	Dual Serial / USB
Dimensions (WxHxD)	21.2 x 13 x 1.5 in (without stand)
Power Supply	AC: AC 110V ± 10%
Operating Temperature	0° - 55° C
Operating Humidity	20% - 80%
Warranty	1 year
Touch Interface	Dual: USB, Serial

AT A GLANCE

- Bezel-free, dual touch solution
- LED back-lit

APPLICATIONS

- Retail
- Self-Service
- Gaming
- Entertainment



CONTACT

220 Tradesmen Dr.
Hutto, Texas 78634
800.320.5944
sales@touchsystems.com