

IRIScan™ Anywhere 3 Wifi

Scan anywhere, go paperless!

Ultra-compact, lightweight and portable, the battery-powered IRIScan™ Anywhere 3 Wifi is the ideal tool to beat paper. Perfect for scanning just about anything at home or on the go, it allows mobile users to easily capture documents, contracts, business cards, receipts and more, without a computer!

Just slip any paper document through the handheld scanner; it is saved automatically into the provided MicroSD™ card and ready to be sent via Wi-Fi to your smartphone, iPad®, iPhone®, Android™ tablet, Windows® or Mac® computer.

But that's not all. The provided world-renowned OCR software suite will extract all key information from your scans easily. Your documents are turned into fully editable files ready to be shared in the Cloud, and your business cards are saved as digital contacts within your favorite contact management system.

Key Features

Mobile scanner

- Battery-powered and ultra-compact. No computer or cables needed to scan!
- Scan up to 100 A4 documents on battery mode.
- Scan directly to JPEG/PDF.
- Scanning resolutions: 300/600/1200 dpi.
- 1.44" TFT Color Display Panel for instant scan preview.
- Scanning speed – A4/Color
 - 300/600 dpi: 12 pages per minute.
 - 1200 dpi: 8 pages per minute.
- Directly save scans into your microSD™ card (up to 32 GB).
- FREE MicroSD™ card included.
- Share your scans via Wi-Fi to ANY device (iOS®/Android™ & PC/Mac®).
- iOS®/Android™ Apps for easy Wi-Fi transfer to tablet & smartphone.

Powerful software suite

- Readiris™: OCR software – Convert any paper document, PDF, or image file into editable Office documents and upload to the Cloud in a click.
- Cardiris™: Business cards recognition software – Scanned business cards are automatically retyped and exported into your favorite contact manager (Outlook®, ACT!®, etc.)

Quick reference guide

Product name	IRIScan™ Anywhere 3 Wifi
SKU	458129
UPC-A code	765010732869
Custom code	847190
MSRP (USD)	\$169
Box size (H x L x D)	5.43 x 12.12 x 2.28 in
Box weight	31.7 oz
Box languages	Arabic, Dutch, English, French, German, Italian, Portuguese, Russian, Spanish
Box content	IRIScan™ Anywhere 3 Wifi scanner • USB cable • Free MicroSD™ card • Calibration sheet • Cleaning cloth • Software suite for PC and Mac® on CD-ROM • Quick user guide on CD-ROM • Quick start sheet

Scanner specifications

Scanner size (H x L x D)	3,5 x 27,5 x 4,4 cm (1.73 x 10.62 x 2.12 in)
Scanner weight	330g (0.73 lbs.)
Document feeding	Automatic document feeding (single page feed type)
Image sensor	contact image sensor (CIS)
Resolutions	300/600/1200 dpi
Scan color	Color/B&W
File Formats	JPEG/PDF
Maximum paper size	Up to A4
Color Display	1.44" Color Display Screen
10 scanner menu languages	English, Spanish, French, German, Italian, Dutch, Russian, Si. & Tr. Chinese, Japanese
Battery	Built-in 1200mAH Li-polymer battery Scanning capacity when fully charged: up to 100 A4 pages
Charging method	USB cable

Minimum computer requirements

Scanner

- At least one USB port available
- Installable on any operating system that supports mass storage protocols

Software suite for Windows®

- Intel® Pentium® based PC or equivalent recommended
- Microsoft® Windows® 8, 7, Vista®, XP
- 512MB RAM recommended
- 500MB of available hard disk space
- CD-ROM drive or internet connection for software download

Software suite for Mac OS®

- Mac® computer with Intel® processor
- Mac OS® X version 10.4 or above (Compatible with Mac OS® X Mavericks)
- 512MB RAM recommended
- 500MB of available hard disk space
- CD-ROM drive or internet connection for software download



© Copyright 2014 IRIS s.a.
All rights reserved for all countries.
IRIS, IRIS' product names, IRIS'
logos and IRIS' product logos are
IRIS trademarks. All other products
and names mentioned are trademarks
or registered trademarks from their
respective owners.

