

B910

4MP Outdoor Mini PTZ with D/N,
Basic WDR, 10x Zoom Lens



- 4 Megapixel with 1080p
- Day & Night
- 10x Zoom Lens with f4.9 - 49mm / F1.8 - 3.0, DC Iris, Auto Focus
- Basic WDR (70 dB)
- 30 fps at 1920 x 1080
- Pan & Tilt
- Weatherproof (IP67) and Vandal Proof (IK10)


PHOTO INDICATION



- ① Ethernet Port
- ② DC 12V Power Input
- ③ Digital Input / Output and Audio-In / Audio-Out

- ④ Reset Button
- ⑤ Memory Card Slot

DIMENSION DIAGRAM



Unit: mm [inch]

ACCESSORY OPTIONS

Dome Cover		
PDCX-1104		Smoked dome cover for B9X, vandal proof (IK10)

Power Supply		
PPOE-0001		PoE Injector IEEE 802.3af compliant, AC 100-240V, with universal connectors
PPBX-0002		AC 100-240V to DC 12V power adapter with universal connectors

Popular Mounting Solutions	
Surface	Accessories not required
Wall	PMAX-0314
Pendant	PMAX-0101 + PMAX-0103
Corner	PMAX-0314 + PMAX-0402
Pole	PMAX-0314 + PMAX-0503
Gang Box	PMAX-0804

* For more mounting solutions, please refer to Mounting Accessory Selector on www.acti.com

PRODUCT SPECIFICATION

B910

• Device

Device Type	Outdoor Mini PTZ Camera
Image Sensor	Progressive Scan CMOS
Sensor Size	1/3"
Effective Pixels	2688 (H) x 1520 (V) (4.09 MP)
Horizontal Resolution	1500 TVL
Day / Night	Yes
Low Light Sensitivity	Standard
Minimum Illumination	Color: 0.1 lux at F1.8 (30 IRE, 2400°K); B/W: 0.05 lux at F1.8 (30 IRE, 2400°K)
Color to B/W switch	ISP based switch, configurable
Mechanical IR Cut Filter	Yes
IR Sensitivity Range	700 - 1100nm
IR LED	No
Electronic Shutter	1/5 ~ 1/2,000 sec (manual mode); 1/5 ~ 1/10,000 sec (auto mode)
S/N Ratio	52 dB

• Lens

Focal Length	Zoom, f4.9 - 49mm / F1.8 - 3.0
Zoom Ratio / Speed	10x optical / Max. 2 secs
Zoom Application	Camera Installation; Auto Zoom by Event; Manual Operation
Iris	DC iris
Focus	Auto focus
Horizontal Viewing Angle	54.13° ~ 6.65°

• PTZ

Manual Panning Speed	0.1° - 190°/s
Manual Tilting Speed	0.1° - 150°/s
Preset Panning Speed	0.1° - 190°/s
Preset Tilting Speed	0.1° - 150°/s
Panning Range	-175° - 175° (without auto-flip)
Tilting Range	0° - 180° (with E-flip)
Control	Remote manual control; 256 preset points; 10 preset tours; Auto scan
Preset Panning Accuracy	1.5°
Preset Tilting Accuracy	1.5°
Absolute Position	Yes
Protocol	ACTi URL command, Sony VISCA, Pelco D, Pelco P

• Video

Compression	H.264 (Baseline / Main / High profile), MJPEG
Max. Frame Rate vs. Resolution	15 fps at 2688 x 1520; 15 fps at 2560 x 1440; 30 fps at 1920 x 1080; 30 fps at 1280 x 720; 30 fps at 800 x 600; 30 fps at 640 x 480; 15 fps at 320 x 240
Multi-Streaming	Simultaneous dual streams based on two configurations
Bit Rate	28 Kbps - 6 Mbps (per stream)
Bit Rate Mode	Constant, Variable
Privacy Mask	4 configurable regions for each of 17 preset points
Image Enhancement	Basic WDR (70 dB); White balance: automatic, hold and manual; Brightness; Contrast; Sharpness; Automatic gain control; 2D+3D digital noise reduction; Flickerless;
Text Overlay	User defined text on video
Image Orientation	Image flip and mirror

• Audio

Audio	2-way
Compression	8 kHz, Mono, PCM, 16 bit encoding; G.711
Audio-In	Terminal block
Audio-Out	Terminal block

• Network

Protocol & Service	TCP, UDP, HTTP, HTTPS, DHCP, PPPoE, RTP, RTSP, IPv4, IPv6, DNS, DDNS, NTP, ICMP, ARP, IGMP, SMTP, FTP, UPnP, SNMP, Bonjour, Sony VISCA, Pelco D, Pelco P
Ethernet Port	1, Ethernet (10/100Base-T), RJ-45 connector
Security	IP address filtering; HTTPS encryption; Password protected user levels; Anonymous login; IEEE 802.1X network access control

• Alarm

Alarm Trigger	Video motion detection (3 regions); External device through digital input; Sound detection
Alarm Response	Notify control Center; Change camera settings; Command other devices; E-mail notification with snapshots; Save video or snapshot to local storage; Upload video or snapshot to FTP server; Activate external device through digital output

• Interface

Digital Input	1, Terminal block
Digital Output	1, Terminal block
Local Storage	MicroSDHC/MicroSDXC memory card slot (card not included)

• General

Power Source / Consumption	PoE Class 3 (IEEE802.3af) / 11.2 W (built-in heater and fan on) DC 12V (adapter not included) / 7.8 W (built-in heater and fan on)
Weight	1306 g (2.88 lb)
Dimensions (Φ x H)	153 mm x 115 mm (6" x 4.5")
Environmental Casing	Weatherproof (IP67 rated); Vandal proof (IK10 rated), Transparent dome cover
Mount Type	Surface, Pendant, Wall, Corner, Pole, Flush, Gang box
Starting Temperature	-30°C ~ 50°C (-22°F ~ 122 °F) within 30min
Operating Temperature	-40°C ~ 50°C (-40°F ~ 122 °F)
Operating Humidity	10% ~ 85% RH
Approvals	CE (EN 55022 Class B, EN 55024), FCC (Part15 Subpart B Class B), IP67, IK10, NEMA 4X, UL (for optional PoE injector and power adapter)

• Integration

Unified Solution	Fully compatible with ACTi software
ISV Integration	Software Development Kit (SDK) available; ONVIF Compliant
GPS Position	Manual setting
Firmware Access Browser	Microsoft Internet Explorer 8.0 or newer (full functionality) Safari with QuickTime installed, and other browsers with VLC installed (partial functionality)

* All specifications are subject to change without notice.

* All brand names and registered trademarks are the property of their respective owners.

www.acti.com

