


DS-2CE55C2N-IRM


720 TVL PICADIS Outdoor IR Dome Camera



Key features

- 1/3" PICADIS
- 1.3MP Sensor: 1280 (H) x 960 (V) Effective Pixels
- 720 TVL Horizontal Resolution
- True Day/Night
- 2.8/3.6/6mm Fixed Lens, 0.1 lux /F1.2
- 20m IR Distance
- Smart IR, high dynamic range
- Superior video image output and ultra low light illumination
- Wide operating temperature range
- IP66 Weatherproof

Dimensions



DS-2CE55C2N-IRM	
Camera	
Image Sensor	1/3" PICADIS
Signal System	NTSC
Effective Pixels	1280 (H) × 960 (V)
Min. Illumination	0.1 Lux @ (F1.2, AGC ON), 0 Lux with IR
Shutter speed	NTSC: 1/30 s to 1/30,000 s
Lens	3.6 mm (2.8mm, 6 mm optional)
	Angle of view: 71.4° (3.6 mm)
Lens Mount	M12
Angle Adjustment	Pan: 0 - 360° , Tilt: 0 - 75° , Rotation: 0 - 360°
Day & Night	IR cut filter with auto switch
Horizontal Resolution	720 TVL
Synchronization	Internal synchronization
Video Output	1Vp-p composite output (75 Ω/BNC)
S/N Ratio	More than 62 dB
General	
Working Temperature/Humidity	-40 ° C - 60 ° C (-40 ° F - 140 ° F) Humidity 90% or less (non-condensing)
Power Supply	12 V DC
Power Consumption	Max. 1.5W (Max. 4.5W with IR cut filter on)
Ingress Protection	IP66
IR Range	20 meters
Dimensions	89.6 × 59.1 mm (3.53" × 2.33")
Weight	400 g (0.88 lbs)

Available models

DS-2CE55C2N-IRM

Accessories



DS-1229ZI-1
(Wall Mount)



DS-1239ZI-1
(Wall Mount)