

|                        |                         |
|------------------------|-------------------------|
| Part Number            | NSVK080-101R15TL        |
|                        | Basic, Non-Surge        |
| Power Configuration    | 15A, 120V, 1.4kW        |
| Physical Configuration | 24 in / 610 mm Vertical |



|                 |                                                                                                                          |
|-----------------|--------------------------------------------------------------------------------------------------------------------------|
| Description     | The NSVK080-101R15TL non-surge unit is ideal for facilities already equipped with surge protection.                      |
| Product Summary | NSVK080-101R15TL - Non-Surge, 15A, 120V, Vertical, (8) NEMA 5-15R, power switch, breakered, 10 ft power cord with L5-15P |
| Monitoring      | None                                                                                                                     |
| Plug Form       |  L5-15P                               |
| Receptacle      |  NEMA 5-15R (Quantity: 8)             |

## NSVK080-101R15TL - Product Specification and Options

|                                         |                                 |
|-----------------------------------------|---------------------------------|
| Quantity Of Inputs                      | 1                               |
| Voltage                                 | 120V                            |
| Current                                 | 15A                             |
| VA per Input (Load Capacity)            | 1.4kW                           |
| Frequency                               | 50/60 Hz                        |
| Over Current Protection                 | 15A Thermal Breaker             |
| Switch                                  | Yes                             |
| Indicators - LED(s)                     | 1 - Power ON Green LED          |
| Power Cable Wire Gauge                  | 14/3                            |
| Power Cable Length                      | 10ft                            |
| Plug Type                               | NEMA L5-15P Twistlock           |
| Receptacle/Socket Type #1               | NEMA 5-15R                      |
| Quantity on Face #1                     | 8                               |
| Center to Center Receptacle Spacing     | 2.0                             |
| Style #1                                | Individual - Rotated            |
| Maximum Output per Receptacle/Socket #1 | 15A                             |
| Voltage per Receptacle/Socket #1        | 120V                            |
| Heavy Steel -Black Powder Coat          | Yes                             |
| Configuration                           | 24in / 600mm Vertical Rackmount |
| Plastic Mounting Clips                  | 1 - Bottom; 1 - Top             |
| Made in the USA                         | Yes                             |
| Product Warranty                        | Lifetime                        |
| Certification/Agency Approvals          | RoHS Compliant                  |
| Certification/Agency Approvals          | UL & c-UL Listed 60950          |
| Chassis Dimensions (LxWxD)              | 24.00in x 1.61in x 1.61in       |
| Shipped Weight                          | 5lbs (2.27kg)                   |

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
[www.geistglobal.com](http://www.geistglobal.com)

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100  
[www.geisteurope.com](http://www.geisteurope.com)

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.  
Postal Code: 518000  
Tel: +86.755.86639505  
[www.geistglobal.com](http://www.geistglobal.com)

### Geist Asia

Hong Kong  
Tel: +852 90361927  
Email: [salesasia@geistglobal.com](mailto:salesasia@geistglobal.com)