

## MFCJ5720DW Technical Specifications

A fully featured model in the Business Smart range of professional inkjet printers, the MFCJ5720DW is designed around increasing office productivity. A 2-sided, 50 sheet Automatic Document Feeder makes scanning, copying, and faxing fast and hassle-free. High yield ink cartridges, coupled with a paper capacity of 580 sheets ensure that the printer is always ready – allowing your team to focus on your business.

Print 3.0 is all about convenient printing. You can scan and share documents across your existing wired or wireless network, or print from your mobile devices through Brother's iPrint&Scan app, Apple AirPrint or Google Cloud Print. You can also connect directly to the web from your printer to scan to; or print from, Google Drive, FLICKR®, Dropbox, Picasa™, OneDrive, Facebook, Box, EVERNOTE™ and OneNote.

The MFCJ5720DW is also able to print in A3 paper sizes, and in A4 at speeds of up to 22ipm (mono) and 20ipm (colour). This all owes your business to present professional, high quality output without the wait, while high capacity ink cartridges print up to 2,400 pages help conserve resources without sacrificing on quality.

All Brother inkjet multifunction printers incorporate an ink system with four individual ink cartridges – meaning you only need to replace the ink that runs out – reducing waste and saving you money. The MFCJ5720DW is also compliant with strict ENERGY STAR, Blue Angel and Nordic Swan environmental standards to ensure low energy consumption, low noise levels and a recycle-friendly design.

### GENERAL

Memory capacity	256MB
Connectivity	USB 2.0, Wireless 802.11b/g/n, Ethernet 10/100BASE-TX
Mobile connectivity	iPrint&Scan app, AirPrint, Google Cloud Print™, Wi-Fi Direct
Display	9.3cm touchscreen colour LCD

### COLOUR PRINTER

Speed (laser comparable)*	Up to 22ipm mono & 20ipm colour
2-sided print	Automatic up to A4
Resolution	Up to 6,000 x 1,200 (Vertical x Horizontal)
Borderless printing	Available for A3, A4, LTR, A6, Photo 10x15cm, Photo-L, Photo 2-L, Index Card, Postcard
Minimum droplet size	1.5pl (when used with Brother BP71 paper, see Supplies section)

### COLOUR FAX

Modem	33.6kbps
Speed dials	100 locations for pre-stored numbers
Page memory	Up to 200 pages (ITU-T Test Chart No 1)
Error correction mode	Yes
Other functions	Fax forwarding, remote access, fax retrieval, dual-access, I-Fax**, PC-Fax send, PC-Fax receive***, auto reduction, group dials

### COLOUR COPIER

Speed	Up to 12ipm mono & 9ipm colour
Resolution	1,200 x 2,400dpi (colour & mono)
Multi copy	Yes (99 copies)
Enlargement / reduction ratio	25% - 400%
Other features	N-in-1, Poster Printing, Automatic 2 sided copy

### COLOUR SCANNER

Resolution	Optical: Up to 2,400dpi Interpolated: Up to 19,200dpi
Scan speed	From 3.37 seconds mono & colour @ 100dpi
Scan format	JPEG, BMP, PDF, TIFF, PNG (USB Flash Memory Drive supports PDF mono & colour, JPEG, TIFF).
Other features	Automatic 2 sided scan
Scan to	Email / OCR / Image / File / Card / USB Flash Drive / FTP / Network** / E-mail server** / web services

### PAPER HANDLING

Paper Input	250 sheet standard paper tray up to A3 250 sheet lower paper tray up to A3 80 sheets (up to A4) or 5 sheets (up to A3) rear multi-purpose tray 50 sheet 2-sided automatic document feeder (ADF) One sheet manual feed slot up to A3
Paper Output	50 sheets
Paper Handling Sizes	Landscape: A4, LTR, EXE. Portrait: A3, LGR, LGL, A5, A6, Photo, Indexcard, Photo-L, Photo-2L, C5, Com-10, DL Envelope, Monarch
Media Type	Plain, Inkjet, Glossy, Transparency

\* ISO/IEC 24734

\*\*Optional free download available from <http://support.brother.com>

\*\*\*Windows® only

\*\*\*\*Approx. cartridge yield is declared in accordance with ISO/IEC 24711

### DIRECT PRINT AND SCANNING

USB Media Cards	PictBridge, USB Flash Memory Drive Memory Stick Duo/Pro Duo/Micro, Secure Digital (SD), Secure Digital High Capacity (SDHC), Secure Digital Extended Capacity (SDXC), Multimedia Card, Multimedia Card Plus, Multimedia Card Mobile
Direct print format	JPEG
Direct scan format	JPEG, PDF (colour), TIFF, PDF (mono)

### SOFTWARE

Driver software included	Brother MFL-Pro Suite
Software - Windows®	Brother ControlCentre4, Nuance Paperport® 12 SE with OCR,
Software - Macintosh®	Brother ControlCentre2, NewSoft® Presto!® PageManager9
Supported operating systems	Windows® 8 Windows® 7 Windows Vista® Windows® XP Windows Server® 2003 & 2003 R2 Windows Server® 2008 & 2008 R2 Windows Server® 2012 & 2012 R2 Mac OS X v10.7.5/10.8.x/ 10.9.x

### SUPPLIES

Standard cartridges	LC233 BK/C/M/Y black & colour - approx 550**** A4 pages
High yield cartridges	LC235 XL C/M/Y colour - approx 1,200**** A4 pages
Super high yield cartridges	LC239 XL BK black - approx 2,400**** A4 pages
Brother paper	BP71GA3: A3 glossy photo paper, 20 sheets BP71GLA: A4 glossy photo paper, 20 sheets BP71GLP: 4x6" glossy photo paper, 20 / 50 sheets BP60MA: A4 matte inkjet paper, 25 sheets BP60PA: A4 inkjet paper, 250 sheets



### WEIGHTS & DIMENSIONS

With carton	W589 x D425 H429mm 17.8Kg
Without carton	W490 x D345 x H308mm 14.5Kg

### OTHERS

Power consumption	Operating - 32W Ready - 5.5W Sleep - 1.8W Off - 0.04W
Sound pressure level (operating)	50dBA Average



# MFCJ5720DW

**brother**  
at your side

# IT's the Business. Redefining Printing.



**PRINT - SCAN - COPY - FAX**

THE ALL-IN-ONE INKJET THAT REDEFINES  
PRINTING FOR YOUR BUSINESS

**brother**  
at your side

[www.brother.co.nz](http://www.brother.co.nz)

Contact:

## INTRODUCING

# THE MFCJ5720DW

## REDEFINING OFFICE PRINTING FOR YOUR BUSINESS

Experience a new level of office printing with the MFCJ5720DW. Intelligent, fast, and more connected, it's the perfect choice to help raise your team's productivity. Take advantage of A3 printing to create high impact documents, while save on overheads through high capacity ink for low cost per print.

The MFCJ5720DW also includes features such as cloud connectivity and direct mobile printing – essential in today's fast-paced world.



### COST EFFECTIVE

Super high yield ink cartridges capable of printing up to 2,400 black and 1,200 colour prints, combined with other cost-saving features like 2-sided printing and ink save mode help to lower your total cost of ownership.



### ENHANCED CONNECTIVITY

With built-in wireless and wired LAN, the cloud connected MFC-J5720DW ensures seamless collaboration between team members. Scan to and print directly from cloud services such as Dropbox, Evernote™, OneDrive and Google Drive to digitise paper-based content to share among your team in seconds.



### PRODUCTIVE

The MFC-J5720DW comes packed with a range of productivity solutions to help streamline your business. Fast print and scan speeds, paired with the two sided automatic document feeder help to quickly capture and share vital information



### PROFESSIONAL

Ensure that your business is noticed with high quality A3 size printing. Two high capacity paper trays and a versatile rear paper tray offer your team the option to print what they want, when they want.



### MOBILE INTEGRATION

Agile businesses are constantly ahead when it comes to technology. With built-in support for mobile print and scan solutions, your team can print and scan anywhere, anytime. Brother's iPrint & Scan app provides seamless compatibility with Apple, Android and Windows devices, allowing you to improve productivity levels.

