



Performance & Use

- Eliminate monthly rental fees—Up to \$120 per year¹
- Cable Internet speeds up to 340 Mbps[†]—8 downstream & 4 upstream channels
- Gigabit Ethernet port for faster access and downloads
- CableLabs® DOCSIS® 3.0 Certified to work with cable Internet providers XFINITY® from Comcast, Spectrum®, Cox®, Cablevision and more



Overview

The NETGEAR CM400 High Speed Cable Modem provides a connection to high-speed cable Internet with speeds up to 340 Mbps[†]. It is CableLabs® certified and with DOCSIS® 3.0 is 8X faster than 2.0. A Gigabit Ethernet port provides faster access and downloads.


The NETGEAR Difference - CM400

- Gigabit Ethernet port
- DOCSIS® 3.0 CableLabs® certified
- Supports IPv6
- Secure connection
- Easy installation

¹Based on a typical monthly equipment rental fee of \$10 per month.

Fast Cable Internet Access

- Up to 340 Mbps[†] download and upload speed for streaming HD videos, faster downloads, and high-speed online gaming
- CableLabs® Certified for US cable Internet services - DOCSIS® 3.0 is 8 times faster than DOCSIS 2.0 devices
- Works with U.S. cable Internet providers like XFINITY® from Comcast, Spectrum®, Cox®, Cablevision & more (not compatible with Cable bundled voice services)
- Fast self-activation for XFINITY customers—Get connected without a service call
- Save money over time by owning your cable equipment and avoiding monthly rental charges from your Internet provider
- Gigabit Ethernet port—Fastest wired speeds to connect your router or computer



Connect the CM400 High Speed Cable Modem directly to your computer or wireless router for connecting to other wireless devices.

PACKAGE CONTENTS

- High Speed Cable Modem—DOCSIS 3.0 (CM400)
- Stand
- Ethernet cable
- Quick install guide
- Power adapter

PHYSICAL SPECIFICATIONS

- Dimensions: 5.8 x 3.8 x 1.8 in (147 x 96 x 30 mm)
- Weight: 0.44 lb (0.19 kg)

WARRANTY

- www.netgear.com/warranty

ADVANCED FEATURES

- Designed to meet DOCSIS 3.0 specifications and backward compatible with DOCSIS 2.0 networks
- Fast download and upload speed - 8 x4 Channel Bonding enables 340 Mbps¹ download
- IPv6 next generation Internet addressing support
- Gigabit Ethernet port with auto-sensing technology

TECHNICAL SPECIFICATIONS


- Simple—CD-less installation
- Memory: 8MB flash and 64MB DDR
- Advanced Quality of Service (QoS)
- IPv6 support (Internet Protocol Version 6)

SYSTEM REQUIREMENTS

- Cable broadband Internet service
- Please check your cable Internet service provider web site for data speed tier compatibility
- Microsoft® Windows® 7, 8, 10, Vista®, XP®, 2000, Mac OS®, or other operating systems running a TCP/IP network
- Microsoft® Internet Explorer® 5.0, Firefox® 2.0, Safari® 1.4, or Google Chrome™ 11.0 browsers or higher

STANDARDS

- One (1) LAN Gigabit Ethernet port
- One (1) WAN coaxial cable connection



This product comes with a limited warranty that is valid only if purchased from a NETGEAR authorized reseller.

*90-day complimentary technical support following purchase from a NETGEAR authorized reseller.

¹Maximum rate is derived from DOCSIS® 3.0 specifications and actual throughput will vary depending on the MSO provisioning and speed tier subscription. Check your cable Internet service provider web site for data speed tier compatibility.

NETGEAR makes no express or implied representations or warranties about this product's compatibility with any future standards.

Customer-owned modems may not be compatible with certain cable networks. Please check with your cable provider to confirm this NETGEAR modem is allowed on your cable network. This product is not compatible with Cable bundled voice services.

For indoor use only.

NETGEAR, and the NETGEAR Logo are trademarks of NETGEAR, Inc. Mac, Mac OS and the Mac logo are trademarks of Apple Inc., registered in the U.S. and other countries. Any other trademarks mentioned herein are for reference purposes only. ©2017 NETGEAR, Inc.