




FEATURES

- OVER 450 TVL
- 3D Comb Filter with De-Interlace and Noise Reduction
- HDMI, analog composite and VGA Video inputs
- 1 Looping BNC Output
- Certification: FCC, CE, and CB
- 50,000 Hour Rated Lifespan
- Construction Black Plastic Bezel and Removable Base

INCLUDED ACCESSORIES

- 1x VGA Video Cord
- 1x Power Cord
- 1x Manual
- 3.5mm Audio Cord

BACK PANEL INPUTS & OUTPUTS



MENU OPERATION



Menu buttons are located on the back of the panel on the right side of the bezel.

SOURCE: Selects HDMI, VGA, BNC, or S-Video input.

UP/Down: Select setting to adjust move

LEFT/RIGHT: Increase/Decrease values

Menu: Active menu for picture adjustments

Power: Turn On/Off Monitor

SPECIFICATIONS

Model	AVG19WBV-3D
Size	18.5"
Aspect	16:9
Native Resolution	1366 x 768 @ 60Hz
Colors	16.7M
Viewing Angle	H: 170 V: 160
Viewing Lines	700 TVL
Contrast Ratio	1000:1
Response Time	5ms
Comb Filter w/ De-Interlace	3D Comb Filter w/ De-Interlace
Noise Reduction	3D Noise Reduction
Brightness	250cd/m ²
Speakers	2 (3 watts each)
Composite Video In	1x BNC, 1x RCA
Composite Video Out	1x BNC
HDMI Input	1x HDMI
VGA Input	1x VGA
Audio Input/Output	1x Audio In, 1x Audio Out (Stereo 3.5mm jack)
Auto Adjustment	Yes
Wall Hanging	VESA Standard
VESA Size	100 x 100mm
Stand / Bezel	Plastic
OSD Language	English and Spanish
Power Consumption	<25W, <0.5W (Standby)
Power Supply	AC100-240V, 50/60Hz
Dimension L x D x W	17.8" x 13.42" x 7.3"
Packing Dimension	19.5" x 14.8" x 4.5"
Net Weight	6.17 lbs / 2.8 Kg
Operating Temp.	32 ~ 104° F / 0 ~ 40° C
Certifications	FCC, CE, and CB