

# VDO360

## COMPASS SPECIFICATIONS

- Focus range/depth of field: f4.9 – 49mm/60cm-infinity
- Optical distortion: 1.2% -+0.8%
- Dynamic range: 65db
- SNR: 50db above
- FOV: Diagonal 66.6-7.2, Horizontal 53.2-5.3, Vertical 39.8-4.2
- Sensor size: 1/2.7"
- Standard Center Tripod mount: 1/4"/20 thread
- MJPEG Format with resolution at 640×480, 1280×720, and 1920×1080 all at 30fps.
- USB2.0 output
- RS232 control, compatible with all major control systems
- UVC Control over USB, software for Near End Camera Control included (download)
- Dual IR receiver on front
- Belt Drive Stepper motors with variable speed
- 9-12V DC input at 1A
- W 4 5/8" (117.5mm) , D 4 3/8" (111.2mm) , H 5"(127mm)
- Weight: 1lb 3.2 Oz , (.548 Kg)



3432 South River Terrace, Edgewater MD 21037  
855-443-2492 or 307-200-7448  
[www.vdo360.com](http://www.vdo360.com)