

High speed 4-in-1 for productive home office with Wi-Fi and cloud connectivity

**MAXIFY MB2350**

you can



## Fast, productive Wi-Fi All-In-One for the home office with cloud connectivity

Fast and productive All-In-One offering business quality colour printing for home offices. Features Wi-Fi and Ethernet, touch screen operation plus smartphone and cloud connectivity.

### Key Features

- Fast All-In-One for the busy home office with print, copy, scan and fax functions
- No waiting for documents with Quick First Print plus 15 colour pages/min and 23 mono pages/min
- Wi-Fi plus Ethernet connection: print from and scan to PCs, smartphones, tablets and cloud services
- Integrated 50-sheet Automatic Document Feeder and 500-sheet paper capacity
- Print up to 1,200 mono and 900 colour pages with individually replaceable XL ink tanks
- Create quality documents with Dual Resistant HD ink optimised for business printing
- Recommended monthly page volume of 200-1,000 pages
- Easy operation with large 7.5 cm colour touch display

### What's in the Box

MAXIFY MB2350, Power cable, Set up ink tanks, Set up CD for Windows (Mac drivers available online), Manuals, Fax/phone line cable

### Dimensions (W x D x H)

463 x 389 x 320 mm

### Supported OS

**Windows** 8.1 / 8 / 7 / Vista SP1 & SP2 / XP SP3 32-bit  
**Windows Server** 2003, 2003 R2, 2008, 2008 R2, 2012, 2012 R2  
**Mac OS** X v10.6.8 or later



PRINT



COPY



FAX



SCAN

**Canon**

# MAXIFY MB2350


## Specifications



- 1 Flatbed, ADF
- 2 Upper cassette: 250 sheets of plain paper  
Lower cassette: 250 sheets of plain paper
- 3 PGI-1500XL BK (1200 pages)  
PGI-1500XL C (1020 pages)  
PGI-1500XL M (780 pages)  
PGI-1500XL Y (935 pages)  
Colour ink tanks (CMY) average yield: 900 pages

<b>OVERVIEW</b> Summary Functions	Fast, productive All-In-One for home offices Print, Copy, Scan, Fax, Wi-Fi, Ethernet + Cloud Link
<b>PRINTER SPECIFICATIONS</b> Print Speed (approx.) First Page Out Time (approx.) Print Technology Maximum Print Resolution Print Margins (min.) 2-Sided Printing	23.0 ipm mono A4 <sup>[1]</sup> 15.0 ipm colour A4 <sup>[1]</sup> Mono: 7 sec (ready) / 11 sec (sleep) Colour: 9 sec (ready) / 14 sec (sleep) Inkjet, FINE print head 600 x 1200 dpi Top: 3mm, Bottom: 5mm, Left & Right: 3.4mm Automatic (A4, LTR plain paper)
<b>SCANNER SPECIFICATIONS</b> Scanner Type Scanner Technology Scanner Resolution (Optical) Maximum Document Size Scanning Depth (Input / Output) Scan Functions	Flatbed, ADF CIS colour scanner Up to 1200 x 1200 dpi <sup>[2]</sup> Flatbed: A4, LTR (216x297mm) ADF: A4, LTR, LGL Colour: 48 bit / 24 bit Greyscale: 16 bit / 8 bit Scan to email, Scan to network folder, Scan to Cloud, Scan to USB
<b>COPIER SPECIFICATIONS</b> Copy Speed (approx.) Multiple Copy Reduction / Enlargement Copy quality settings Copy functions	ADF colour: 10 ipm <sup>[3]</sup> ADF mono: 21 ipm <sup>[3]</sup> Up to 99 pages 25-400%, Fit to Page Standard, High Frame Erase, Collate, 2-on-1, 4-on-1
<b>FAX SPECIFICATIONS</b> Fax Type Fax Resolution Fax Speed Fax Memory Coded Speed Dialling Group Dial	Super G3 / Colour Mono: up to 300 x 300dpi Colour: 200 x 200 dpi Mono: approx. 3 sec. (33.6kbps) <sup>[4]</sup> Colour: approx. 1 min. (33.6kbps) <sup>[4]</sup> Up to 250 pages Max. 100 locations Max. 99 locations
<b>INKS &amp; YIELD</b> Ink Type XL Inks	Dual Resistant High Density ink 4 ink tanks (Black, Cyan, Magenta, Yellow) PGI-1500XL BK (1200 pages) <sup>[5]</sup> PGI-1500XL C (1020 pages) <sup>[5]</sup> PGI-1500XL M (780 pages) <sup>[5]</sup> PGI-1500XL Y (935 pages) <sup>[5]</sup> Colour ink tanks (CMY) average yield: 900 pages <sup>[5]</sup>
<b>PAPER SUPPORT</b> Paper Types Maximum Paper Input Paper Sizes Paper Weight	Plain Paper Envelopes (DL, COM10) Canon High Resolution Paper (HR-101N) Canon Matte (MP-101) Canon Pro Luster (LU-101) Canon Plus Semi-gloss (SG-201) Canon Plus Glossy II (PP-201) Canon Glossy Everyday Use (GP-501) Upper cassette: 250 sheets of plain paper Lower cassette: 250 sheets of plain paper Plain paper: A4, A5, B5, LTR, LGL (upper and lower cassette) Photo paper: A4, LTR, 20x25cm, 13x18cm, 10x15cm (upper cassette) Custom sizes: Width 89-215.9 mm, Length 127-355.6 mm Plain paper: 64 - 105 g/m <sup>2</sup> Canon photo paper up to 275 g/m <sup>2</sup>

<b>CONNECTIVITY</b> Wired Connections Wireless Connections Applications Support	Hi-Speed USB 2.0 Ethernet 10/100Mbps (auto switchable) USB flash memory port (A type) Wi-Fi IEEE802.11 b/g/n <sup>[6]</sup> Access Point Mode MAXIFY Printing Solutions app MAXIFY Cloud Link (from printer screen or smart device) Canon Print Service plug-in (Android) Apple AirPrint Google Cloud Print Print from Email
<b>SOFTWARE</b> Supported Operating System Supported Mobile Systems Minimum System Requirements Software Included	Windows 8.1 / 8 / 7 / Vista SP1 & SP2 / XP SP3 32-bit Windows Server 2003, 2003 R2, 2008, 2008 R2, 2012, 2012 R2 Mac OS X v10.6.8 or later iOS Android Windows RT Windows: Internet Explorer 8, internet connection or CD-ROM Mac: Safari 5 and internet connection Display: 1024x768 or higher Canon Quick Toolbox Scanning Utility Easy-WebPrint EX (for Windows)
<b>GENERAL FEATURES</b> Display Type & Size Automatic Document Feeder Dimensions (W x D x H) Weight Power Source Power Consumption Typical Electricity Consumption Noise Levels Recommended Operating Environment Duty Cycle (monthly) Recommended Print Volume	7.5cm colour touch screen Up to 50-sheets 463 x 389 x 320 mm 463 x 459 x 320 mm (paper installed) 12.2kg AC 100-240V, 50/60Hz Standby: Approx. 1.0 W (USB connection to PC, scanning lamp off) Off: Approx. 0.3 W Copying: Approx. 29 W <sup>[7]</sup> 0.3 kWh <sup>[8]</sup> Approx. 54 dB(A) <sup>[9]</sup> Temperature: 15-30°C Humidity: 10-80%RH (no dew condensation) up to 15,000 pages <sup>[10]</sup> 200-1000 pages / month
<b>Footnotes</b>	<sup>[1]</sup> Document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard. <sup>[2]</sup> Optical resolution is a measure of maximum hardware sampling resolution based on ISO 14473 standard. When scanning in high resolution, the scan size is restricted. <sup>[3]</sup> ADF copy speed is the average of ESAT simplex, ISO/IEC 24735, excluding time to copy the first set. <sup>[4]</sup> Based on default setting using ITU-T No.1 chart for mono and Canon Colour Fax Test Sheet for colour. <sup>[5]</sup> Page yield is based on ISO/IEC 24711 and continuous printing. Printer ships with setup ink tanks: 400 pages black (BK) and 300 pages colour (C/M/Y average). <sup>[6]</sup> Wi-Fi frequency band: 2.4GHz, Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP, Administration password <sup>[7]</sup> When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings. <sup>[8]</sup> Typical Energy Consumption (TEC) represents the typical electricity consumed by a product during one week. <sup>[9]</sup> Acoustic Noise is measured based on ISO7779 standard. <sup>[10]</sup> Duty cycle is defined as a maximum number of printed pages for a single peak month.
<b>Standard disclaimers</b>	All specifications subject to change without notice. Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc. Copy speed may vary depending on document complexity, copy mode, page coverage; type of paper used etc. and does not take into account warming up time. Actual fax transmission speed may vary depending on document complexity, fax settings at receiving end, and line conditions etc. Ink yield may vary depending on documents printed, applications software used, print mode and type of paper used. For more information see <a href="http://www.canon-europe.com/ink/yield">www.canon-europe.com/ink/yield</a> All brand and product names are trademarks of their respective companies.



Canon Inc.  
canon.com

Canon Europe  
canon-europe.com

English Edition  
© Canon Europa N.V., 2014

High speed 4-in-1 for  
productive home  
office with Wi-Fi and  
cloud connectivity

**MAXIFY MB2350**  
you can



Fast, productive Wi-Fi All-In-One for  
the home office with cloud connectivity

Sales Start Date: **October 2014**

**The whole range consists of:**

MAXIFY MB5350, MAXIFY MB5050, MAXIFY iB4050,  
**MAXIFY MB2350**, MAXIFY MB2050

**Box Dimension (W x D x H)**

472 x 555 x 512 mm

**Box Weight (G/N)**

16.2 / 12.3 kg

**Package Style**

Pallet

**Quantity of item**

8

**MERCURY CODES**

**PRODUCT**

Name	Mercury Code	EAN Code
MAXIFY MB2350 EUR	9488B009AA	4549292008401
MAXIFY MB2350 GB	9488B008AA	4549292008395

**OPTIONS**

Consumables	Mercury Code	EAN Code
PGI-1500XL BK	9182B001AA	4549292003772
PGI-1500XL C	9193B001AA	4549292003888
PGI-1500XL M	9194B001AA	4549292003901
PGI-1500XL Y	9195B001AA	4549292003918



PRINT



COPY



FAX



SCAN

**Canon**