

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SmartRack 5U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: SRWF5U36











Wall-mount cabinet secures and organizes 5U of 19-inch rack equipment in locations with limited floor space. Houses servers and other equipment up to 36 inches deep, but extends less than 10 inches from wall.

Description

The SRWF5U36 SmartRack 5U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends less than 10 inches from the wall while housing equipment up to 36 inches deep, including 1U servers, UPS systems, battery packs, network switches and patch panels. In addition to 5U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF5U36 comes fully assembled and ready to mount to the wall. Equipment installation is easy, with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable WorkspacePerfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the wayHouses EIA-standard 19 in. rack equipment in 5U of spaceExtends less than 10 in. from wall while housing equipment up to 36 in. deep, including 1U servers, UPS systems, battery packs, network switches and patch panelsSlide-out 2U mounting bracket for patch panels up to 2.5 in. deepMaximum

Highlights

- Maximum load capacity of 150
 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 5U of 19 in. rack equipment up to 36 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF5U36 SmartRack 5U
 Low-Profile Vertical-Mount
 Server-Depth Wall-Mount Rack
 Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



load capacity of 150 lbs (68 kgs)

Keeps Important Equipment SecureTop panel and reversible front door lock securely to help prevent damage, tampering or theftVented cabinet keeps equipment coolConvenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment InstallationShips fully assembled for quick installationWall-mounting holes spaced 16 in. apart for standard wall stud placementRails adjust easily—unscrew them, slide them to desired depth, and screw them back inThreaded mounting holes support M6 or 12-24 mountingRack spaces marked for easy reference

Meets Payment Card Industry StandardsProvides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

| OVERVIEW | |
|-------------------------------------|-------------------------------------|
| UPC Code | 037332183729 |
| Device Compatibility | Patch Panel; Network Switch; Server |
| Rack Type | Enclosure |
| PHYSICAL | |
| Color | Black |
| Maximum Device Depth (cm) | 91.44 |
| Maximum Device Depth (in.) | 36 |
| Maximum Device Depth (mm) | 914 |
| Rack Height | 5U |
| Shipping Dimensions (hwd / cm) | 32.51 x 71.12 x 115.57 |
| Shipping Dimensions (hwd / in.) | 12.80 x 28.00 x 45.50 |
| Shipping Weight (kg) | 34.47 |
| Shipping Weight (lbs.) | 76.00 |
| Unit Dimensions (hwd / cm) | 109.73 x 65.02 x 24.64 |
| Unit Dimensions (hwd / in.) | 43.2 x 25.6 x 9.7 |
| Unit Weight (kg) | 33.57 |
| Unit Weight (lbs.) | 74 |
| Weight Capacity - Stationary (kg) | 68 |
| Weight Capacity - Stationary (lbs.) | 150 |
| Rack Depth | Standard |
| Number of Vertical Mounting Rails | 2 |
| SPECIAL FEATURES | |
| Built-in Cable Management | No |
| Extra Wide | No |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| STANDARDS & COMPLIANCE | |
|-------------------------------------|-----------------------------------|
| Certifications | EIA-310-E; IP20 Protection Rating |
| Approvals | RoHS |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies