



U3477PQU

86.4cm (34") LCD MONITOR

This imposing 34-inch monitor stretches out in 21:9 format with 3440 x 1440 resolution for wider viewing and more room to multitask. IPS technology delivers extra-wide viewing angles of up to 178 degrees.



SCREEN+



DVI



PIVOT



HDCP



VESA



ZEROSWITCH



E-SAVER



I-CARE

GENERAL FEATURES

Line	Pro-line
Panel Type	IPS
Panel Size	34" / 86.4 cm
Aspect Ratio	21:9
Brightness	320 cd/m²
Contrast Ratio Dynamic	80M:1
Pixel Pitch (H) (V)	0
Display Area (H x V)	799.8 x 334.8
Viewing Angle (CR >= 10)	178/178
Response time	5ms GTG
Color	Black

SCANNING FREQUENCY

Scanning Frequency	30-83khz/ 56-75hz
Pixel Frequency	205MHz (VGA) / 300MHz (DVI/HDMI) / 600MHz (DP)

RESOLUTION

Maximum Resolution	3440 x1440@60Hz
Recommended Resolution	3440 x 1440@60Hz
Colors	1.07 Billion
HDCP compatible	Yes

CONNECTORS

D-Sub	Yes
DVI	Yes
HDMI	1x
USB	No
MHL	Yes
DisplayPort	1

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 47,54, Standby: 0,28W, Off: 0,19W
Zero Power Switch	Yes

OTHER FEATURES

Plug and Play	Yes
Speakers	Yes
Headphone Out	Yes
Wallmount	100x100mm
Height Adjustment	180mm
Pivot	Yes
Swivel	Yes
Tilt	-5/+24

Regulations	Energystar 6 TCO 6 EPEAT Silver TUV-GS TUV-Bauart CE FCC EAC RoHS compliant
-------------	---

Specific Features	Multiview iCare i-Menu e-Saver Screen+ Vesa Wallmount
-------------------	--

ACCESSORIES

VGA Cable
DVI Cable
Displayport Cable
Audio Cable
USB Cable
USB 2.0 Micro Cable
Power Schuko C7 Cable

DIMENSIONS

Product with stand (W×H×D)	551.4x400.4x221 mm
Packaging (W×H×D)	953x127x435 mm
Weight	10 kg wo/packaging 13.74 kg w/packaging
Warranty	3 Years
EAN	4038986114769