



Photographic printing, refined.

The all-new Epson® SureColor P600 features Epson UltraChrome® HD Ink for extraordinary exhibition-quality prints. With unprecedented black density and breakthrough Resin Encapsulation Technology, the P600 delivers the richest blacks with an incredible level of sharpness. Three-level Black Ink technology delivers smooth tonal transitions for the finest black-and-white prints. High-capacity, individual ink cartridges improve your productivity with fewer user interventions. Advanced media handling allows you to easily print with a wide variety of fine art and roll papers. Create borderless 13" x 19" prints and panoramas over 10 feet long. Whatever you print, the SureColor P600 delivers such dramatically bold images, it sets a groundbreaking new benchmark in photographic quality.

P-Series

Highlight Details

Specs

Feature	Description
Dimensions and Weight	SureColor P600 24.2" (W) x 32" (D) x 16.7" (H) Printing 33 lb 24.2" (W) x 14.5" (D) x 9" (H) Storage
Printing Technology	Advanced MicroPiezo® AMC™ Print head with Ink Repelling Coating Technology Nozzle Configuration: 8 channels of 180 nozzles Maximum Resolution: Up to 5760 x 1440 dpi with a 2.0 pl minimum droplet size
Printer Interface	Includes as standard one Hi-Speed USB 2.0 and one Ethernet Port (10/100 Base-T)
Software	Epson Professional Imaging Communication Drivers for Windows® and Macintosh® Epson Printer Utilities
Operating Systems Supported	Microsoft® Windows 8, Windows 7, Macintosh Yosemite (10.10), Mavericks (10.9), Mountain Lion (10.8), Lion (10.7)
Epson UltraChrome HD Ink	Cartridge fill volume — 25.9 ml each color x 9 colors total Ink cartridge shelf life (recommended) — 2 years from printed production date or 6 months after opening P-Series printers are designed to be used exclusively with the specially-formulated Epson inks, and not with other brands of cartridges or inks
What's in the Box	Printer Set of initial ink cartridges CD/DVD tray Power cord User Guide Kit (Printer basics guide, CD-ROM with Windows and Macintosh utilities and Professional Driver Software, Start Here poster) Roll paper holders Accessory box
Electrical Requirements	Voltage: AC 100 – 240 V Frequency: 50 – 60 Hz
Power Consumption	Operating: Approx. 20 W Sleep: Approx. 1.4 W Power Off: Approx. 0.15 W
Regulatory Standards	UL (MET), FCC (Class A), CSA, CE, EMC
Operating Conditions	Temperature: 50° to 95°F Relative Humidity: 20 – 80% (no condensation)
Limited Warranty and Service	Standard one-year, usually third-business-day service with phone support Monday through Friday

Better Products for a Better Future™
eco.epson.com

Epson America, Inc.
3840 Kilroy Airport Way, Long Beach, CA 90806
proimaging.epson.com

Epson Canada Limited
185 Renfrew Drive, Markham, Ontario L3R 6G3
proimaging.epson.ca

Specifications and terms are subject to change without notice. EPSON, Epson UltraChrome, MicroPiezo and SureColor are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future is a trademark of Seiko Epson Corporation. AMC is a trademark of Epson America, Inc. Macintosh is a trademark of Apple Inc., registered in the U.S. and other countries. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2014 Epson America, Inc. CPD-42478 12/14