



PRO-SERIES

900
TVL



Professional All-Purpose Security Camera

PRO-970™

Pro quality 900 TV lines, day/night protection from above!

- See more with high resolution 900 TV lines Swann TruColor video, powerful infrared night vision & wide dynamic range for clear images in any light
- Use the On-Screen Display (OSD) controller & built-in software to customize the camera settings for professional video surveillance
- Easily mount to walls with heavy duty, vandal-resistant aluminum construction & IP66 weatherproof rating for all conditions
- Fight back against crime by deterring intruders & protecting your property
- Plug into your DVR for recording or TV's yellow video-in socket for immediate surveillance
- Perfect for longer range viewing of cars, driveways, warehouses, alleys, hallways etc

900
TVL
HIGH RESOLUTION

AMAZING HIGH RESOLUTION
900TVL VIDEO SENSOR

DIY
DO-IT-YOURSELF

PERFECT FOR DO-IT-YOURSELF
SURVEILLANCE AT HOME OR BUSINESS

NIGHT VISION

POWERFUL DAY & NIGHT VISION
OF 114FT / 35M

OSD
CONTROL

CONTROL VIDEO IMAGE SETTINGS
REMOTELY WITH ON-SCREEN DISPLAY

WEATHER PROOF

IP66 DURABLE WEATHERPROOF
METAL CASING

TV
TV CONNECTION

EASILY CONNECT TO TV & LATEST
DVRS INCLUDING 960H, D1 & MORE

Professional All-Purpose Security Camera

PRO-970™

What's in the box

All installation accessories included

- PRO-970™ Dome Camera
- OSD Controller
- BNC Cable 60ft / 18m
- BNC to RCA Adapter
- Power Adapter
- Mounting Screws & Plugs
- Operating Instructions
- Theft Deterrent Stickers



Specifications

PRO-970™ Camera

Video

Image Sensor	Swann TruColor
Video Quality	900 TV Lines
Day/Night Mode	Color during day / switches to B&W at night

Wide Dynamic Range	Adjustable
Lens	6mm
Viewing Angle	45 degrees

Night Vision

Night Vision Distance	114ft / 35m
Number of Infra-Red LEDs	30

General

Indoor / Outdoor	Indoor or outdoor, IP66 rated
Operating Power	DC 12V
Operating Temperature	-4°F ~ 122°F / -20°C ~ 50°C
Body Construction	Aluminum
Dimensions – Camera	7.85" x 3.35" x 2.75" 200mm x 85mm x 70mm
Weight – Camera	0.87lbs / 395g
Cable Length	60ft / 18m

Code

Swann Code	SWPRO-970CAM
------------	--------------

Easily mount to walls or ceilings



It's as easy as 1, 2, 3



1
Select a Swann Pro-Series camera

2
Connect to OSD controller in pack

3
View & control your camera through a Swann DVR, monitor or TV

Installation is easy

Do-it-Yourself

Installing this Swann product is simple. For instructions, tips and videos see the operating instructions in this pack or visit www.swann.com

Professional Installation

Need extra help?

We have an installer in your region!

For more visit www.swann.com



Our Promise

Swann stands by its promise of Lifetime Support to make advanced security easy to use, install and maintain. Everything is in the pack but if you need it Swann's help desk is available 24 hours a day, 7 days a week for the life of the product.

For more information on this product visit
www.swann.com