

Peace of Mind IP Cameras



KEEP A WATCHFUL EYE ON YOUR HOME

Legrand IP Security Cameras

Providing clear, high-definition images, even in total darkness, Legrand Indoor and Outdoor IP cameras are the ideal solution for any homeowner. While at home, view live camera feed on networked computers and devices. While away, remote access and control is convenient with the Legrand Camera app. All cameras install easily over a single-gang electrical box and are powered with a single PoE cable.

At Home or On-the-Go

Peace of mind is always at hand with the Legrand Camera app for iOS and Android devices. View live feed remotely on smart phones and tablets, and designate motion-triggered recording or email alerts for an added sense of security.

FEATURES:

- View live feed and receive email alerts with the Legrand Camera app
- High Definition image resolution
- IR operation for 24/7 viewing, even in total darkness
- ONVIF compliant for third-party integration
- Installs easy and is powered by a single PoE cable

BENEFITS:

Convenient Control, On-the-Go View live feed remotely on smart phones and tablets with the Legrand Camera app for iOS and Android devices.

Don't Miss A Thing IR operation allows 24/7 viewing, even in total darkness. Designate motion triggered recording and receive email alerts.

The Complete Solution Integrates with Intuity home automation for complete, unified home control.

Three Flexible Options



Outdoor IR HD Bullet
Camera (CM7000)



Outdoor IR Dome Camera
with Zoom (CM7020)



Indoor IR HD Wall Mount
IP Camera (CM7100)

IP CAMERAS



Outdoor IR HD Bullet Camera (CM7000)



Outdoor IR Dome Camera with Zoom (CM7020)



Indoor IR HD Wall Mount IP Camera (CM7100)

SPECS	CM7000 - Outdoor Bullet Camera	CM7020 - Outdoor Dome Camera	CM7100 - Indoor Cube Camera
Image Sensor:	1/3", 1.2 Megapixel CMOS	1/3" 4 Megapixel CMOS	1/3", 1.2 MegaPixel CMOS
Focal Length:	3.6 mm fixed focal length @ F1.8	2.8-8mm 2.8x motorized lens@ F1.8	4.2mm fixed focal length @ F1.8
Field of View Range @ 50 Feet	66.7' (W) x 50' (H)	Max Zoom: 30' (W) x 22.5' (H) Wide Angle: 85.7' (W) x 64.3' (H)	57.1' (W) x 42.9' (H)
Day & Night Mode:	42 IR LEDs covering up to 33 Feet (10 meter)	10 850nm IR LEDs covering up to 50 Feet (15 meter)	10 IR LEDs covering up to 15 Feet (4.6 meter)
Max Video Resolution:	1280x960 (25 FPS) or 1280x720 (30 FPS)	2688x1520 (30 FPS) or 1920x1080 (30 FPS)	1600x1200 (25 FPS) or 1280x720 (30 FPS)
Audio Input:	3.5 mm Line-In, 1,500 ohms, 0.1Vrms ~ 0.707Vrms	N/A	Integrated Microphone
Audio Output:	3.5 mm Line-Out, 600 ohms, 0.707Vrms	N/A	Integrated Speaker
Micro SDHC Card Support:	N/A	Up to 36 GB (Class 10)	Up to 36 GB (Class 10)
Network Port:	10M/100M Auto Sensing, RJ45	10M/100M Auto Sensing, RJ45	10M/100M Auto Sensing, RJ45
Power over Ethernet (PoE):	IEEE 802.3af, class 0	IEEE 802.3af, class 0	IEEE 802.3af, class 0
Wireless:	N/A	N/A	802.11 b/g/n (2GHz)
Dimensions (W x H):	3.7in (D) x 9.1in (L) (94mm (D) x 230mm (L))	4" W x 3 1/4" H (105mm W x 82.2mm H)	3.7in (D) x 9.1in (L) (94mm (D) x 230mm (L))
Weather Rating	IP66	IP66	N/A
Vandal Resistant	N/A	IK10	N/A

Note all devices include: Web Browser Microsoft IE 6.0 or above, Firefox (H.264 requires add-in).

Mobile IP Camera Viewer iOS 4.3 or above, Android 1.6 or above.

designed to be better™

 **legrand**®

Legrand, North America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca