

VxRGB True Candle LED Lamp with Flicker Effect, 1900K, 50 lumens

- 1900K color temperature – Warm, gentle light; closely matches that of a real candle flame.
- Light gently and randomly flickers – just like a real candle!
- Ideal for decorative lighting fixtures, including those settings where use of actual candles is unsafe or impractical
- Reduces energy consumption compared to traditional incandescent lamps.
- 25,000 hour lifetime* reduces maintenance costs.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- 3-Year Limited Warranty



Specifications

Lamp Type	True Candle 1900K with Flicker
Model	CD-L50-C19-VXFLM-G
Wattage	2.5W
Lumen Output	50 lm
Efficacy	20 lm/W
Color Temperature	1900K
CRI	85
Beam Angle	-
Dimmable	No
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E12
Weight	2.04 oz.
Design life	25,000 Hrs.
Part Number	98812