

Designed for Home Office and Small Business



- Display**
 - 24-inch 16:9 LED (1920x1080)
- CPU Support**
 - 4th generation Intel Core i3, i5 & i7 processors
- Chipset**
 - Intel® H81
- Memory**
 - 2 x DDR3 204-pin SO-DIMM sockets populated up to 8GB Max.
- HDD Support**
 - Integrated Serial ATA controller
- Video & Graphics**
 - Intel HD graphics 4600
- Networking**
 - 1x Gigabit (Gbe)
- Audio**
 - Integrated speakers at the bottom of the unit
 - Integrated HD audio
- Swivel base**
 - Tilting base-stand (non-swivel)

- I/O Ports**
 - 2x USB 3.0
 - 1x USB 2.0
 - 1x HDMI
 - 1x RJ45
 - DC In (19V)
 - Audio Ports
- Power Supply**
 - 150W 100 ~ 240V AC, 50-60Hz.
 - Supports Output range: DC 19V, 7.9A
- Touch Screen**
 - Capacitive Multi-Touch
- Wireless**
 - 802.11 b/g/n
- Webcam**
 - Integrated 1.3MP webcam
- Wall Mount**
 - Supports both 75mm & 100mm VESA mounting holes
- Expansion Slots**
 - Two Mini PCI-e (1xFull-size and 1xHalf-size)

O/S	• Windows 8, Windows 7	Weight	• Unit: 18.05 lbs
Environment	• Ambient Temperature: 0°C ~ 40°C (operating)	Dimensions	• 26"W x 18"H
Relative Humidity	• 10% ~ 90% (non-condensing)	Colors	• White
		Certifications	• FCC class B, CE



Corporate Headquarters
Cybernet Manufacturing
5 Holland
Irvine, CA 92618
Toll free: 888-834-4577
Local: 949-600-8000
Fax: 949-600-8013
www.cybernetman.com
sales@cybernetman.com
support@cybernetman.com

Cybernet Europe
Network House, Hawkins Road
Colchester, Essex CO2 8LA
United Kingdom
UK Phone: 0845-539-1200
UK Fax: 0845-539-1201
www.cyberneteuropa.com
sales@cyberneteuropa.com
support@cyberneteuropa.com

Cybernet Taiwan Company, LTD.
4F., No.25, Lane 140, Xingai Rd
Neihu District, Taipei City 11494
Taiwan (R.O.C.)
Phone: (02) 2790-4776
Fax: (02) 2793-3172
www.cybernet.com.tw
sales@cybernet.com.tw
support@cybernet.com.tw