

AOC Monitors
LED monitor

27 Series

27" Class, 1920 x 1080

E2727SHE



Slim Design with Eco-Friendly and User-Friendly Features

The E2727SHE offers stunning image quality at 1920 x 1080 resolution, while providing features that benefit you. The 27-inch class monitor is eco-friendly, both Energy Star and EPEAT Silver certified, with AOC's eSaver software to set low-power configuration and iMenu software to access the user-friendly On Screen Display. Slim in design while offering vibrant images with 20M:1 contrast ratio, the E2727SHE also has a 3.5mm earphone jack and VESA 100mm wall mount compatibility.

Key Features

- 27" viewable image with 16:9 aspect ratio
- VGA, DVI-D with HDCP, HDMI connectivity
- 3.5mm Earphone out jack for headphone use
- VESA 100mm wall mount compliant
- Slim design to complement room decor



Windows 8
Windows RT
Compatible

AOC

Slim in Design

AOC's E2727SHE has a slim design that is perfect for saving desktop space, while giving you the optimum 27" viewable image screen with 16:9 aspect ratio. The LED backlit monitor runs a maximum 1920 x 1080 resolution.

**Clear Visibility and Vibrant Images**

With a 20,000,000:1 contrast ratio and 5ms response time, the E2727SHE provides vibrant images and reveals darker image areas in greater depth. You can watch videos or play games without missing a beat.

**User-Friendly and Eco-Friendly Features**

The E2727SHE comes with VGA, DVI-D with HDCP, HDMI connectivity, and a 3.5mm earphone jack for when you want to listen to music or watch movies in privacy. The VESA 100mm Wall Mount compliant feature allows you to have the monitor mounted on the wall with the appropriate mounting accessory. The E2727SHE is Energy Star and EPEAT Silver certified with low-power consumption, and comes with AOC's eSaver and iMenu software for both eco-friendly and user-friendly configuration and navigation.

E2727SHE Specifications



E2727SHE



Cabinet Color	Glossy Black Bezel and Base	
Panel	TFT Active Matrix LCD, LED Backlight 27" Class, 16:9 Aspect Ratio 27" Viewable Image Size, Diagonal	
Pixel Pitch	0.311mm x 0.311mm	
Display Area	597.89mm(H) x 336.31mm(V)	
Brightness	300 cd/m ² (typical)	
Contrast Ratio	20,000,000:1 (dynamic)	
Response Time	5ms (typical)	
Viewing Angle	Horizontal: 170 Degrees (CR>10) Vertical: 160 Degrees (CR>10)	
Scanning Frequency	Horizontal: 30K~83KHz Vertical: 50~75 Hz	
Optimal Resolution	1920x1080x60Hz	
Recommended Resolution	1920x1080@60Hz	
Supported Resolutions	640x480@60Hz/67Hz/72Hz/75Hz	640x400@70Hz
	720x400@70Hz	800x600@56Hz/60Hz/72Hz/75Hz
	832x624@75Hz	1024x768@60Hz/70Hz/72Hz/75Hz
	1440x900@60Hz	1680x1050@60Hz
	1920x1080@60Hz	
Color Depth	16.7M	
Connectors	1 x 15-pin VGA 1 x DVI-D with HDCP 1 X HDMI	
Audio	Earphone out (3.5mm Jack) x1	
User Control	Auto/Power	
Adjustability	Tilt: -2° ~ +20°	
Power Source	Universal 110~240VAC, 50/60Hz	
Power Consumption	Power On: <18W, Standby: < 0.5W	
Regulations	CE,FCC, UL, RoHS, EPA Energy Star®, EPEAT® Sliver, Windows 8	
Other Features	Extra narrow bezel, VESA 100mm Wall Mount Compliant ¹ , Includes AOC's e-Saver, Screen+ and iMenu software	
Dimensions (WxHxD mm)	Monitor: 646.9x455.1x238 Carton: 706x515x135	
Dimensions (WxHxD inches)	Monitor: 25.47x17.92x9.38 Carton: 27.80x20.28x5.31	
Weight (Net)	11.90lbs/5.4KGs	
Weight (Gross)	14.76lbs/6.7KGs	
Loading Qty w/pallet	20'=512 pcs 40'= 1024 pieces	
UPC	685417080281	
What's in the box	27" Monitor, stand and base, Power Cord, VGA Cable, Media (includes drivers, AOC Software, User's Manual, Warranty)	

1. Wall mount arm & bracket not included.

Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trade marks are property of their respective owners.

For more information, visit us.aoc.com or Call 888-838-6388