



AVerCharge L12i

12 Device Intelligent Charge Locker





Built for 12 devices

Charge up to 12 Chromebooks, laptops, or tablets up to 15" screen.



Daisy-chain technology

Charge multiple L12i cabinets through a single outlet with AVer's innovative charging system.



Compact Size

The stackable design of the L12i provides secure storage in even the most confined spaces.




Device Protection

Protect your valuable assets from theft and damage with a three-point steel locking mechanism and foam protected dividers.




Easy cable management

Designed for easy organization, L12i provides individual AC adapter compartments that accommodate a variety of adapters.



Intelligent Charging

When daisy-chaining multiple cabinets, the intelligent charging feature prevents circuit overload by analyzing and regulating power for a safe charge.



Specifications

Device Capacity	12	Cart Dimension	H = 49.5 cm (19.49") W = 76cm (29.92") D = 42.5cm (16.73")
Slot Size	H = 28.5cm (11.22") W = 3.6cm (1.42") D = 36.4cm (14.33")	Package Dimension	H = 66 cm (24.02") W = 92cm (36.22") D = 61cm (24.02")
Supported Devices	Tablet/Chromebook up to 14"	Net weight	33.4kg (73.65lbs)
Charging Type	Power receptable	Gross weight	41kg (90.39lbs)
External Power Outlets	N/A	Cable Management	Individual AC adapter compartments and cable clips
LED Indicator	Status LED (x1): Solid Blue: Charging	Power Specification	AC: 100-120V ~ 50/60Hz, 12A 200-140V ~ 50/60Hz, 8A
Sync Type	N/A	Security	Front doors: 3 point mechanism with lock hole
Sliding Shelves	N/A	Casters	
Divider Type	Metal bar with foaming padding	Security Hook	Yes
Warranty	10 years cart and tray 5 years electrical components	Fan	N/A
AC Adapter compartment dimensions	H = 6.7cm (2.64") W = 4.9cm (1.95") D = 10cm (3.94")	Wireless AP holder dimensions (optional)	N/A

Aver Information Inc. Americas

averusa.com

668 Mission Court, Fremont, CA 94539

T 408.263.3828

F 408.263.8132

toll free 1.877.528.7824