



## RCMBN243-102PK3PS56-OD-IP67

**Part Number:** RCMBN243-102PK3PS56-OD-IP67

**Category:** Switched

**Sub Category:** Unit Level

**Power Configuration:** 20A, 230/400V WYE, 11.0kW

**Physical Configuration:** 66 in / 1682 mm, Vertical



### Description:

The RCMBN243-102PK3PS56-OD-IP67 provides hands-on control remotely. While Monitored PDUs can display information remotely, this Switched unit offers the ability to use that information and stay in control of individual power outlets. The RCMBN243-102PK3PS56-OD-IP67 manages whatever issues arise with the click of a few buttons on a smart phone or computer. Also, disable problem equipment by cutting power to specific outlets, reboot equipment remotely by turning power on and off, and save time and money by avoiding sending live technicians to the source of the issue.

**DCIM Enabled** - The RCMBN243-102PK3PS56-OD-IP67 easily integrates with Geist DCIM software, which collects and reports critical power and environmental data for multiple PDUs in a single user interface. Users gain immediate remote access to trends, alarms and histories of devices in the data center through a standard Web browser. Geist DCIM saves both time and cost associated with managing each device individually. Contact your Geist rep for more details.

---

### Product Summary:

RCMBN243-102PK3PS56-OD-IP67 - Switched, Unit Level, + Environmental Monitoring -- 20A, 230/400V WYE, 3 Phase, Vertical, (21) Locking IEC C13, (3) Locking IEC C19, 10 ft power cord with 3P+N+E (IP67), Input and per Phase power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display. Black Powder Coat.

---

### Monitoring:

Input and per Phase power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display.

---

Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

Geist Europe

+44 (0) 1823.275100  
geistglobal.com

Geist Asia

China  
+86.755.86639505  
geistglobal.com

**Plug Form:**

3P+N+E (IP67)

**Receptacle:**Locking IEC C13  
(Quantity: 21)Locking IEC C19  
(Quantity: 3)**Geist Americas**800.432.3219  
[geistglobal.com](http://geistglobal.com)Geist DCIM  
1.877.449.4150  
[geistglobal.com](http://geistglobal.com)**Geist Europe**+44 (0) 1823.275100  
[geistglobal.com](http://geistglobal.com)**Geist Asia**China  
+86.755.86639505  
[geistglobal.com](http://geistglobal.com)

**Product Specification and Options:**

|   |   |
|---|---|
| Monitoring                                | Input and per Phase power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display. |
| Monitoring Level 1                        | Aggregate - Total Unit Monitoring (kWh, W, VA, PF)  |
| Monitoring Level 2                        | Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A)   |
| Remote Power Management                   | Individual Outlet Switching with Optional User Defined Time Delays with Sequential Power-up   |
| Quantity Of Inputs                        | 1   |
| Voltage                                   | 230/400V WYE  |
| Current                                   | 20A x 3 Phase WYE   |
| VA per Input (Load Capacity)              | 11.0kW  |
| Frequency                                 | 50/60 Hz  |
| Over Current Protection                   | None  |
| Switch                                    | No  |
| Indicators - LED(s)                       | 24  |
| Activity LED                              | 1   |
| Idle LED                                  | 1   |
| Power LED                                 | 1   |
| Scrolling Digital Display                 | Yes   |
| Power Cable Wire Gauge                    | 13/5 (2.5mm <sup>2</sup> )  |
| Power Cable Length                        | 10ft  |
| Plug Type                                 | IEC60309 3P + N + E, 20A, Watertight IP67   |
| Combined Total Receptacle/Socket Quantity | 24  |
| Receptacle/Socket Type #1                 | Locking IEC C13   |
| Quantity on Face #1                       | 21  |
| Quantity per Phase #1                     | 7   |
| Style #1                                  | Individual  |
| Maximum Output per Receptacle/Socket #1   | 15A   |
| Voltage per Receptacle/Socket #1          | 230V  |
| Receptacle/Socket Type #2                 | Locking IEC C19   |
| Quantity on Face #2                       | 3   |
| Quantity per Phase #2                     | 1   |
| Style #2                                  | Individual  |
| Maximum Output per Receptacle/Socket #2   | 16A   |
| Voltage per Receptacle/Socket #2          | 230V  |
| Internal RMS Voltage Sensor               | Yes   |
| Internal RMS Current Sensor               | Yes   |

|   |   |
|---|---|
| Network Connection                                    | Ethernet via RJ45   |
| Network Protocols Supported and Data Access Formats   | ARP, IPv4, IPv6, ICMP, ICMPv6, NDP, TCP, UDP, DNS, HTTP, HTTPS, SMTP, SMTPS, DHCP, SNMP (v1/v2c/v3), Syslog, SSH, Serial, LDAP, JSON API, Web GUI, CLI, JSON datalog, CSV datalog |
| Reboot Button   | Yes   |
| Serial Connection                                     | RS232 via RJ45  |
| Remote Sensor RJ Connection Jacks                     | 2   |
| RSD - Optional Remote Display Jack                    | Yes   |
| Continuous Operating Temperature Range                | 10-45C / 50-113F  |
| Heavy Steel - Powder Coat Finish                      | Black   |
| Configuration   | 66in / 1682mm Vertical Rackmount  |
| 7938 Vertical Mounting Bracket Kit                    | Yes   |
| Toolless Mounting Hardware - Center to Center Spacing | 61.25in and 64.75in   |
| Made in the USA                                       | Yes   |
| Product Warranty                                      | Three Year  |
| Certification/Agency Approvals                        | FCC Part 15 Class A Conformance   |
| Certification/Agency Approvals                        | RoHS Compliant  |
| Certification/Agency Approvals                        | UL & c-UL Listed 60950  |
| Chassis Dimensions (LxWxD)                            | 66.25in x 2.5in x 2.25in  |
| Shipped Weight  | 21lbs (9.53kg)  |

Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

Geist Europe

+44 (0) 1823.275100  
geistglobal.com

Geist Asia

China  
+86.755.86639505  
geistglobal.com