



RCMW248-103PK3TL15-OD

Part Number:	RCMW248-103PK3TL15-OD
Category:	Switched
Sub Category:	Unit Level
Power Configuration:	30A, 208V DELTA, 8.6kW
Physical Configuration:	72 in / 1829 mm, Vertical



Description:

The RCMW248-103PK3TL15-OD provides hands-on control remotely. While Monitored PDUs can display information remotely, this Switched unit offers the ability to use that information and stay in control of individual power outlets. The RCMW248-103PK3TL15-OD manages whatever issues arise with the click of a few buttons on a smart phone or computer. Also, disable problem equipment by cutting power to specific outlets, reboot equipment remotely by turning power on and off, and save time and money by avoiding sending live technicians to the source of the issue.

DCIM Enabled - The RCMW248-103PK3TL15-OD easily integrates with Geist DCIM software, which collects and reports critical power and environmental data for multiple PDUs in a single user interface. Users gain immediate remote access to trends, alarms and histories of devices in the data center through a standard Web browser. Geist DCIM saves both time and cost associated with managing each device individually. Contact your Geist rep for more details.

Product Summary:

RCMW248-103PK3TL15-OD - Switched, Unit Level, + Environmental Monitoring -- 30A, 208V DELTA, 3 Phase, Vertical, (21) Locking IEC C13, (3) Locking IEC C19, breakered, 10 ft power cord with L15-30P, Input, per Phase, and per Circuit/Breaker power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display. Black Powder Coat.

Monitoring:

Input, per Phase, and per Circuit/Breaker power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display.

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia


China
+86.755.86639505
geistglobal.com

Plug Form:



L15-30P

Receptacle:



Locking IEC C13
(Quantity: 21)



Locking IEC C19
(Quantity: 3)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Monitoring	Input, per Phase, and per Circuit/Breaker power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Ethernet and RS232 connectivity. Local LCD display.
Monitoring Level 1	Aggregate - Total Unit Monitoring (kWh, W, VA, PF)
Monitoring Level 2	Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A,B,C) Monitoring (A)
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays with Sequential Power-up
Quantity Of Inputs	1
Voltage	208V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW
Frequency	50/60 Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Indicators - LED(s)	24
Activity LED	1
Idle LED	1
Power LED	1
Scrolling Digital Display	Yes
Power Cable Wire Gauge	10/4
Power Cable Length	10ft
Plug Type	NEMA L15-30P Twistlock
Combined Total Receptacle/Socket Quantity	24
Receptacle/Socket Type #1	Locking IEC C13
Quantity on Face #1	21
Quantity per Breaker and Phase Combination #1	7
Style #1	Individual
Maximum Output per Receptacle/Socket #1	15A
Voltage per Receptacle/Socket #1	208V
Receptacle/Socket Type #2	Locking IEC C19
Quantity on Face #2	3
Quantity per Breaker and Phase Combination #2	1
Style #2	Individual
Maximum Output per Receptacle/Socket #2	16A
Voltage per Receptacle/Socket #2	208V
Internal RMS Voltage Sensor	Yes

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Internal RMS Current Sensor	Yes
Network Connection	Ethernet via RJ45
Network Protocols Supported and Data Access Formats	ARP, IPv4, IPv6, ICMP, ICMPv6, NDP, TCP, UDP, DNS, HTTP, HTTPS, SMTP, SMTPS, DHCP, SNMP (v1/v2c/v3), Syslog, SSH, Serial, LDAP, JSON API, Web GUI, CLI, JSON datalog, CSV datalog
Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	2
RSD - Optional Remote Display Jack	Yes
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	72in / 1832mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	Three Year
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	72in x 2.5in x 2.25in
Doghouse (D)	1.44in
Shipped Weight	22lbs (9.98kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com