

1.9kW Single-Phase Metered PDU, 120V Outlets (6 5-15/20R), L5-20P/5-20P adapter, 0U Vertical, 24-in.

MODEL NUMBER: PDUMV20-24











Features

- 20A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA L5-20P input plug with 15-ft. (4.57 m) line cord and 5-20P adapter
- 0U 24-in. / 61cm vertical rackmount format installs using no rack spaces
- 6 NEMA 5-15/20R outlets
- Includes 20A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Highlights

- Metered single phase 120V 20A 0U 24-in. / 61cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA L5-20P plug and 5-20P adapter
- 6 NEMA 5-15/20R outlets
- Toolless button mount and boltdown bracket installation hardware included

Package Includes

- PDUMV20-24 Metered Vertical
 PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

Specifications

OVERVIEW		
UPC Code	037332182845	
PDU Type	Metered	
INPUT		
PDU Input Voltage	100; 120; 127	
Recommended Electrical Service	20A 120V	
Maximum Input Amps	20	
Maximum Input Amps Details	Agency de-rated to 16A continuous	





PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 20A total capacity (Agency de-rated to 16A); 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Output Nominal Voltage	100; 120; 127
Overload Protection	20A circuit breaker
USER INTERFACE, ALERTS & CO	NTROLS
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated transparent saftey cover
PHYSICAL	
Form Factors Supported	Vertical
Material of Construction	Aluminum
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 67.31
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 26.50
Shipping Weight (kg)	2.86
Shipping Weight (lbs.)	6.30
Unit Dimensions (hwd / cm)	62.2 x 4.2 x 3.81
Unit Dimensions (hwd / in.)	24.47 x 1.64 x 1.5
Unit Weight (kg)	1.60
Unit Weight (lbs.)	3.52
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1: 2007 R10.14 (USA), CAN/CSA-C22.2 No. 60950-1-07+A1:2011+A2:2014 (Canada), NOM (Mexico), FCC Class A (Emissions), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies