

Epson[®] Perfection[®] V39 Color Photo and Document Scanner



The easy-to-use scanner to restore, archive and share photos and more.

High-quality scanning for photos and documents — 4800 dpi optical resolution¹ for amazing clarity and detail

Preserve priceless memories — restore, archive and share family photos for generations to come

Scan to Facebook[®], Google Drive[™] and other cloud services³ — Epson Document Capture Pro and Easy Photo Scan software included

Convenient — easy-to-use buttons for simple scan jobs, plus a space-saving built-in kickstand for vertical placement

Scan oversized prints, documents and artwork — ArcSoft Scan-n-Stitch[®] Deluxe 2 included⁴

Restore color to faded photos — with one click, Easy Photo Fix[®] technology makes it simple

Scan books and photo albums — high-rise, removable lid

Remove dust from scanned photos — Advanced Digital Dust Correction

Convert scanned documents into editable text — Optical Character Recognition (OCR) software included

USB powered — no AC adapter required



*At retail. Excludes specialty receipt scanners.⁵

Specifications

Type
Flatbed Color Image Scanner

Optical Sensor
CIS (Contact Image Sensor)

Optical Resolution¹
4800 dpi

Hardware Resolution
4800 x 4800 dpi

Effective Pixels
40,800 x 56,160 pixels (4800 dpi)

Color Bit Depth
48-bits per pixel internal / 24-bits per pixel external

Grayscale Bit Depth
16-bits per pixel internal / 8-bits per pixel external

Maximum Scan Area
Flatbed 8.5" x 11.7"

Light Source
Three-color RGB LEDs

Scanning Speed²

Color 300 dpi approximately 10 seconds (via USB 2.0)
Color 600 dpi approximately 30 seconds (via USB 2.0)

Features

Buttons
4 Buttons: PDF, Send, Copy and Start

Image Restoration
Epson Easy Photo Fix Technology

Upright Scanning
Built-in stand for upright scanning and storage

Scanner Lid
Removable scanner lid for oversized and thick media

Software Included

Epson Scan with Easy Photo Fix technology, Epson Event Manager, Epson Copy Utility, Epson Easy Photo Scan, Epson Document Capture Pro, ArcSoft Scan-n-Stitch Deluxe (Windows® only)

System Requirements

Microsoft® Windows 8.1, Windows 8, Windows 7, Windows Vista®, Windows XP SP2 or later
Mac OS® X 10.6.x, 10.7.x, 10.8.x, 10.9.x, 10.10.x

General

Reliability
MCFB 10,000 cycles

Scanner Interface
Hi-speed USB 2.0

Operating Temperature
50 ° to 95 °F (10 ° to 35 °C)

Operating Humidity
20 – 80% (no condensation)

Power Supply
USB Interface Bus Power (Micro-B connector)
Rating: 5 V, 500 mA

Power Consumption
Operating: 2.5 W
Ready: 1.1 W

Off: 0.0125 W (when PC is suspended)
Dimensions (W x D x H)
9.9" x 14.4" x 1.5"

Weight

3.4 lb

Warranty
One-year limited warranty in the U.S. and Canada

Eco Features

RoHS compliant
Recyclable product⁷
Epson America, Inc. is a SmartWaySM Transport Partner⁸

What's in the Box

Epson Perfection V39 scanner, USB cable, install CD, setup poster

Ordering Information

Epson Perfection V39

B11B232201

¹ Optical resolution is the maximum scan resolution of the image sensor, using the definition of ISO 14473. | ² Requires Easy Photo Scan software (included). Mac® version requires software download. | ³ With Epson Document Capture software installed on the connected Windows PC or Mac. | ⁴ ArcSoft Scan-n-Stitch Deluxe is available for Windows only. | ⁵ Based on U.S. and Canada NPD retail scanner databases, March 2013. NPD sample period CY2012. | ⁶ Based on letter-sized scans at 300 dpi in Black-and-White, Grayscale or Color Mode, using the USB interface. | ⁷ For convenient and reasonable recycling options, visit www.epson.com/recycle | ⁸ SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.



Epson America, Inc.

3840 Kilroy Airport Way, Long Beach, CA 90806

Epson Canada Limited

185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com

www.epson.ca

EPSON, Easy Photo Fix and Perfection are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future is a trademark of Seiko Epson Corporation. Built to Perform is a trademark of Epson America, Inc. Mac and Mac OS are trademarks of Apple Inc., registered in the U.S. and other countries. Google Drive is a trademark of Google Inc. SmartWay is a service mark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2014 Epson America, Inc. CPD-41805 11/14