

DCP-1612w

Compact Laser Multi-Function Copier



Brother Printers
September 2013

Top Features:

Fast Printing & Copying

- Help increase your productivity with a black print speed up to 21ppm

Wireless Networking

- Easy to set up and share on your wireless network or connect locally via Hi-Speed USB 2.0 interface

Stylish and Compact

- Fits virtually anywhere

High-Quality Output

- Print professional reports, spreadsheets and documents at up to 2400 x 600dpi resolution

Standalone Copying

- No PC required to make copies. ID copy and reduce/enlarge documents from 25-400% in 1% increments

Convenient flatbed

- For easy copying and scanning to email, file and image

High-quality scanning

- With resolutions up to 19,200 x 19,200 dpi

Convenient Paper Handling

- Holds up to 150 sheets, up to legal sized paper

Toner Save Mode

- Help save money by using Toner Save mode for your less critical business documents

Outstanding Support

- We are Canadians serving Canadians. We provide machine-lifetime support including extensive online technical support options such as videos, TWITTER, FACEBOOK and more. We also provide a 1-year limited warranty. We're at your side every step of the way.

DCP-1612w

Compact Laser Multi-Function Copier

Specifications:

Print Technology	Electrophotographic Laser
LCD Display (type/size)	2-line LCD Display
Paper Size	Up to 8.5" x 14" (legal)
Print Speed (maximum)	Up to 21ppm (letter)
Print Resolution (maximum)	Up to 2400 x 600 dpi
Memory (std./max)	32MB / 32MB
Paper Input Capacity (maximum)[∞]	150-sheet capacity paper tray
Standard Interfaces	Wireless 802.11b/g/n, Hi-Speed USB 2.0
Copy Speed (maximum)	Up to 21cpm (letter)
Copy Resolution (maximum)	600 x 600 dpi
Copy Reduction/Enlargement	25% - 400% in 1% increments
Copy Options	Sorting, N-in-1, Multi-copying/stack (up to 99)
Scanner Type	Flatbed
Document Glass Size	8.5" x 11" (letter/A4)
Scan Resolution (maximum)	Optical: Up to 600 x 1200 dpi Interpolated: Up to 19200 x 19200 dpi
Scan To Capability	File, Image, E-mail
Operating Systems Compatibility	Windows®: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista® / Windows® 7, 8, 8.1 / Windows Server® 2003 (32/64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac® OS X® v10.7.5, 10.8.x, 10.9.x Linux
Maximum Monthly Duty Cycle[°]	Up to 10,000 pages
Recommended Monthly Volume[•]	Up to 250 to 1,800 pages
Mobile Device Compatibility[•]	Brother iPrint&Scan
Warranty	1-year limited warranty
ENERGY STAR® QUALIFIED	Yes

Supplies & Accessories*:

TN-1030	Standard Yield Toner (approx. 1,000 pages) [▼]
DR-1030	Drum Unit (approx. 10,000 pages) [^]

Setup Information:

UPC Code	012502639794
Unit Dimensions	385 W x 340 D x 255 H mm
Unit Weight	7.2 Kg
Carton Dimensions	481 W x 436 D x 406 H mm
Carton Weight	9.0 Kg

Carton Contents:

Brother DCP-1612w
Starter Black Toner Cartridge (700 pages) [▼]
DR-1030 Drum Unit (10,000 pgs) [^]
Quick Setup Guide
Installation and Documentation CD-ROM
AC Power Cord



* Additional purchase required.

[∞] Maximum capacity based on using 20 lb. paper.

[°] Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements.

[•] Requires connection to a wireless network. See www.brother.ca for details, availability, and mobile device compatibility.

[•] The recommended range of monthly printed pages to achieve the best possible performance and printer life. Printers are intended to handle occasional usage beyond this range with little or no effect. Consistently printing above the recommended print volume, however, may adversely affect the print quality or life of the machine. It is always best to choose a printer with an appropriate recommended print volume to allow for any anticipated increase in printing needs.

[▼] Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4).

[^] Drum yield is approx., and may vary by type of use.