

# Contour Series Omnidirectional A19 3000K, 800 lumens, 60w Replacement, Dimmable

- 800 lumen, 60W incandescent replacement lamp
- Smooth, streamlined exterior – no visible heat sink fins
- Omni-directional bulb – shadow-free, even light distribution – from an LED!
- 11.5 Watts – Over 80% reduction in energy consumption when compared to traditional incandescent bulbs.
- 40,000 hour design lifetime\* reduces maintenance costs
- Compatible with most commercial dimmers, offering 10-100% dimming performance\*\*
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant, UL listed.
- 5-Year Limited Warranty

\* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on ENERGY STAR life testing requirements.

\*\*Dimming range may vary based on dimmer used.



## Specifications

Lamp Type	Contour Series Omni A19, 3000K, 800lm
Model	A19-L800-C30-B300-D
Wattage	9.5W
Lumen Output	800 lm
Efficacy	84.21 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	300°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	100g
Design life	25,000 hrs
CBCP	NA
Part Number	98950