

Contour Series MR16 (GU5.3) 2700K, 500lm LED Lamp with 38-Degree Beam Angle, 65W Replacement, Dimmable.

- 65W Halogen replacement lamp
- Smooth, streamlined exterior - no visible heat sink fins.
- Reduces energy consumption by over 80% when compared to traditional MR16 lamps.
- 25,000 hour design lifetime reduces maintenance costs.
- Compatible with most commercial dimmers *
- 38-degree beam angle
- 2700K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Cool beam protects illuminated objects from radiated heat.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant.
- UL Listed
- 3-year Limited Warranty

* Dimming range may vary based on dimmer used.



Specifications

| | |
|-----------------------|--|
| Lamp Type | MR16 (GU5.3) 2700K, 500 lm, 38-degree beam angle |
| Model | M16-L500-C27-B38-D |
| Wattage | 7W |
| Lumen Output | 500 lm |
| Efficacy | 71.4 lm/W |
| Color Temperature | 2700K |
| CRI | 80 |
| Beam Angle | 38° |
| Dimmable | Yes |
| Voltage | 12V |
| Operating Temperature | -20°C to 40°C |
| Socket | GU5.3 |
| Weight | 1.76 oz. |
| Design life | 25,000 hrs. |
| CBCP | 1321 |
| Part Number | 98957 |