

# Contour Series MR16 (GU5.3) 3000K, 500lm LED Lamp with 38-Degree Beam Angle, 65W Replacement, Dimmable.

- 65W Halogen replacement lamp
- Smooth, streamlined exterior – no visible heat sink fins.
- Reduces energy consumption by over 80% when compared to traditional MR16 lamps.
- 25,000 hour design lifetime reduces maintenance costs.
- Compatible with most commercial dimmers \*
- 38-degree beam angle
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Cool beam protects illuminated objects from radiated heat.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Listed
- 3-Year Limited Warranty

\* Dimming range may vary based on dimmer used.



## Specifications

Lamp Type	MR16 (GU5.3) 3000K, 500 lm, 38-degree beam angle
Model	M16-L500-C30-B38-D
Wattage	7W
Lumen Output	500 lm
Efficacy	71.4 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	38°
Dimmable	Yes
Voltage	12V
Operating Temperature	-20°C to 40°C
Socket	GU5.3
Weight	1.76 oz.
Design life	25,000 hrs.
CBCP	1321
Part Number	98958