

MR16 (GU10) 3000K 380lm LED Lamp, Replaces 35W, Dimmable

- Halogen replacement bulb
- Smooth, streamlined exterior – no visible heat sink fins.
- 25,000 hour design lifetime* reduces maintenance costs.
- Compatible with most commercial dimmers, offering 10-100% dimming performance**
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Listed
- 5-Year Limited Warranty

* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on Energy Star life testing requirements.



Specifications

Lamp Type	MR16 (GU10), 3000K, 380 lm
Model	G10-L380-C30-B38-N
Wattage	6W
Lumen Output	380 lm
Efficacy	63 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	38°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	GU10
Weight	2.1 oz
Design life	25,000
Part Number	98786