

# Contour Series High CRI PAR20 3000K, 470lm LED Lamp with 25-Degree Beam Angle, 50W Replacement, Dimmable

- 90 CRI, 50W Halogen replacement lamp
- Features non-glare optics to reduce eyestrain and maximize productivity
- 25-degree beam angle
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Compatible with most commercial dimmers, offering 10-100% dimming performance\*
- Reduces energy consumption by over 80% when compared to traditional halogen PAR lamps
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Wet-Rated
- 5-year Limited Warranty

\* Dimming range may vary based on dimmer used.



## Specifications

|                       |   |
|-----------------------|---|
| Lamp Type             | High CRI PAR20 3000K, 470lm, 25-degree beam angle |
| Model                 | P20-L470-C30-B25-90-W                             |
| Wattage               | 7W  |
| Lumen Output          | 470 lm  |
| Efficacy              | 67 lm/W   |
| Color Temperature     | 3000K   |
| CRI                   | 90  |
| Beam Angle            | 25°   |
| Dimmable              | Yes   |
| Voltage               | 120V  |
| Operating Temperature | -20°C to 40°C                                     |
| Socket                | E26   |
| Weight                | 3.9oz   |
| Design life           | 25,000 hrs  |
| CBCP                  | 1179  |
| Part Number           | 98828   |