

Contour Series High CRI PAR20 3000K, 470lm LED Lamp with 40-Degree Beam Angle, 50W Replacement, Dimmable

- 90 CRI, 50W Halogen replacement lamp
- Features non-glare optics to reduce eyestrain and maximize productivity
- 40-degree beam angle
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Compatible with most commercial dimmers*
- Reduces energy consumption by over 80% when compared to traditional halogen PAR lamps
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Wet-Rated
- 5-year Limited Warranty

* Dimming range may vary based on dimmer used.



Specifications

Lamp Type	High CRI PAR20 3000K, 470lm, 40-degree beam angle
Model	P20-L470-C30-B40-90-W
Wattage	7W
Lumen Output	470 lm
Efficacy	67 lm/W
Color Temperature	3000K
CRI	90
Beam Angle	40°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	3.9oz
Design life	25,000 hrs
CBCP	593
Part Number	98829