

# Contour Series High CRI PAR38 3000K, 1200lm LED Lamp with 40-Degree Beam Angle, 120W Replacement, Dimmable

- 90 CRI, 120W Halogen replacement lamp
- Features non-glare optics to reduce eyestrain and maximize productivity
- 40-degree beam angle
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Compatible with most commercial dimmers \*
- Reduces energy consumption by over 80% when compared to traditional halogen PAR lamps
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Wet-Rated
- 5-year Limited Warranty

\* Dimming range may vary based on dimmer used.



## Specifications

Lamp Type	High CRI PAR38 3000K, 1200 lm, 40-degree beam angle
Model	P38-L1200-C30-B40-90-W
Wattage	17W
Lumen Output	1200 lm
Efficacy	70.6 lm/W
Color Temperature	3000K
CRI	90
Beam Angle	40°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	15.20 oz.
Design life	25,000 hrs.
CBCP	2231
Part Number	98853