

# BR30 3000K, 650lm LED Lamp, 65W Replacement, Dimmable

- 65W Halogen replacement lamp
- Smooth, streamlined exterior – no visible heat sink fins.
- High quality, warm white light – ideal halogen replacement bulb
- Reduces energy consumption by over 80% when compared to traditional halogen lamps.
- 25,000-hour design lifetime reduces maintenance costs.
- Compatible with most commercial dimmers\*
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL Listed
- 5-Year Limited Warranty



\* Dimming range may vary based on dimmer used.

## Specifications

Lamp Type	BR30 3000K, 650lm
Model	R30-L650-C30-R
Wattage	8W
Lumen Output	650 lm
Efficacy	81.25 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	110°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	220g
Design life	25,000 hrs
Part Number	98983