


Intensifier IP® Full HD 1080p Indoor/ Outdoor Bullet IP Camera

O2iB6 2.9mm fixed lens, dark grey housing

Features

- See color in low light without IR LEDs
- Supports up to Full HD resolution @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- No problems caused by objects that reflect or absorb IR light sources
- Presets: Indoor, Outdoor, Elevator, Lobby, Hallway & Low Light
- Wide dynamic range (WDR) operation
- Supports H.264 and MJPEG codecs
- 2-way audio communication
- Micro SD card slot (card not included)
- Sensor input and relay output
- Built-in heater and anti-fog glass reduces condensation under any weather condition
- IP66 compliant
- Conformant with ONVIF profile S*
- 2 year warranty



Camera Specifications

Image Sensor Progressive scan 1/3" CMOS, 2.0MP
 Maximum Resolution 1920 x 1080
 Minimum Illumination F1.2, Color: 0.001 lux (Max Intensify)
 White Balance ATW, Manual, Push
 Intensify Selectable / Off
 Exposure Control Yes
 De-Fog Yes
 Backlight WDR, BLC
 DNR 3D (0-20)

Video Specifications

Main Resolution 1920x1080 @ 30fps
 Compression H.264 (HP/MP/BP), MJPEG
 Bitrate Control VBR, CBR
 Multiple Streaming 5 profiles

Audio Specifications

Mono Input 64Kbps G.711 / 32Kbps G.726
 Mono Output 64Kbps G.711

External Terminal Specifications

Ethernet 10/100 Mbps
 Alarm 1 sensor input, 1 relay output
 Video Analog test output
 Audio 1 mic in, 1 line out (3.5mm)
 Power DC jack
 Storage Micro SD slot

Network Specifications

Protocols IPv4, TCP, UDP, RTP, RTSP, HTTP, HTTPS,
 SMTP, FTP, DHCP, UPnP, DNS

Network Specifications (continued)

DDNS support Speco DDNS (free of charge)
 Security User ID & Password protection, IP address filtering,
 digest authentication, user access log
 User Access 8 simultaneous users at D1 resolution
 Number of users may vary depending on resolution

System Specifications

PoE Standard (IEEE 802.3af)
 Analytics Motion detection (3 regions), audio detection
 Alarm Triggers Analytics & sensor input
 Alarm Events FTP video file upload, email image upload,
 micro SD card recording, relay out
 Video Buffer Configurable pre-record & post-record
 Image Settings Privacy mask

Client Specifications

Web Browser Support Windows (Internet Explorer 8 and up, Chrome, Firefox)
 PC Application SecureGuard®

Operating & Unit Specifications

Power Supply PoE, 12VDC (power supply not included)
 Power Consumption 7W
 Operating Temperature -4° F – 122° F
 Operating Humidity 8% - 80% RH
 Unit Dimensions 8.7" (L) x 3" (W) x 3.2" (H)
 Unit Weight 1.7 lbs.
 Certifications FCC, RoHS
 Included in Package Unit, CD (manual, software), mounting screws,
 L wrench

Optional Accessories



CVCJBB
Bullet Camera
Junction Box



INTCM
Corner/Pole
Adaptor



IPPOEINJ1295
12.95W
PoE Injector



PSW5
12VDC
Power Supply

*Visit www.specotech.com for latest ONVIF® support. ONVIF is a trademark of Onvif, Inc. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 3/3/15