

# Ultra High Definition 4K Monitor



The DS-280UHD Ultra High Definition Monitor features 4K resolution for amazing clarity and vivid color reproduction. Multiple inputs makes connecting your new display simple.

## Features:

- Ultra High Definition
- Recommended Resolution: 3840 x 2160
- Display Port & HDMI Inputs
- LED Backlight for cooler operation
- VESA Compatible for easy mounting
- Energy Star Certified
- TAA and EPEAT Compliant
- 3 Year Warranty

DoubleSight Displays	DS-280UHD 28" Ultra High Definition LCD Monitor																																																																																						
Product Name	DoubleSight 28" Ultra High Definition LCD Monitor																																																																																						
Manufacturer SKU#	DS-280UHD																																																																																						
Product Highlights	<p>The DS-280UHD Ultra High Definition Monitor features 4K resolution for amazing clarity and vivid color reproduction. Multiple inputs make connecting your new display simple. The DS-280UHD is Energy Star Certified and comes with a 3 Year Warranty. Like all DoubleSight Products, this Monitor is fully TAA Compliant. The DS-280UHD is VESA compatible and can be mounted on your Desk Top with any one of the DoubleSight Multi Monitor Flex Stands or Single Monitor Flex Arms for a truly custom and ergonomic fit.</p>																																																																																						
Key Selling Points	<p>Ultra High Definition for Amazing Viewing Recommended Resolution 3840 x 2160 The Latest LED Backlight Technology Light Weight and VESA Compatible for Easy Mounting Built In Speakers</p>																																																																																						
Features and Specs	<table border="1"> <tbody> <tr> <td>LCD</td><td>Panel Type</td><td>TN</td></tr> <tr> <td></td><td>Visible Screen Area</td><td>28"</td></tr> <tr> <td></td><td>Pixel Pitch</td><td>0.16mm x 0.016mm</td></tr> <tr> <td></td><td>Max. Visible Angle</td><td>170°/160°</td></tr> <tr> <td></td><td>Displayed Color</td><td>1.073 Billion Colors</td></tr> <tr> <td></td><td>Response Time</td><td>5 msec (GTG)</td></tr> <tr> <td></td><td>Brightness</td><td>300 cd/m²</td></tr> <tr> <td></td><td>Aspect Ratio</td><td>16:9</td></tr> <tr> <td></td><td>Contrast Ratio</td><td>1000:1</td></tr> <tr> <td></td><td>Recommended Resolution</td><td>3840 x 2160</td></tr> <tr> <td>Interface</td><td>Interface</td><td>Digital</td></tr> <tr> <td></td><td>Interface Type</td><td>(1) Display Port, (3) HDMI Ports</td></tr> <tr> <td>Power</td><td>Power Adapter</td><td>DC 24V, 3.5Amp</td></tr> <tr> <td rowspan="15">Characteristics</td><td>Operating Temperature</td><td>0~40°C</td></tr> <tr> <td>Storage Temperature</td><td>-20°C ~ 60°C</td></tr> <tr> <td>Operating Humidity</td><td>50% RH</td></tr> <tr> <td>Controls</td><td>Graphic OSD, Auto Adjustment</td></tr> <tr> <td>Color</td><td>Black</td></tr> <tr> <td>Audio</td><td>Yes</td></tr> <tr> <td>Adjustable Monitor Stand</td><td>Tilt</td></tr> <tr> <td>VESA</td><td>100mm x 100mm Compatible</td></tr> <tr> <td>Speakers</td><td>2 Rear Mounted (5W)</td></tr> <tr> <td>Overall Dimensions</td><td>17.5"H x 26"W x 6.75"D overall</td></tr> <tr> <td>Monitor Only Dimensions</td><td>15.5"H x 26"W x 2.35"D monitor only</td></tr> <tr> <td>Base Dimensions</td><td>11"W x 6.75"D</td></tr> <tr> <td>Weight</td><td>14.5 lbs</td></tr> <tr> <td>Carton Dimensions</td><td>28" x 20" x 6"</td></tr> <tr> <td>Shipping Weight</td><td>17 lbs</td></tr> <tr> <td rowspan="7">Package Contents</td><td>UPC Code</td><td>816220001495</td></tr> <tr> <td>Certifications</td><td>Energy Star</td></tr> <tr> <td>Warranty</td><td>3 year limited warranty, parts and labor</td></tr> <tr> <td>Monitor</td><td></td></tr> <tr> <td>AC Adaptor and Power Cord</td><td></td></tr> <tr> <td>HDMI Cable, Audio Cable</td><td></td></tr> <tr> <td>CD and Manual</td><td></td></tr> </tbody> </table>		LCD	Panel Type	TN		Visible Screen Area	28"		Pixel Pitch	0.16mm x 0.016mm		Max. Visible Angle	170°/160°		Displayed Color	1.073 Billion Colors		Response Time	5 msec (GTG)		Brightness	300 cd/m²		Aspect Ratio	16:9		Contrast Ratio	1000:1		Recommended Resolution	3840 x 2160	Interface	Interface	Digital		Interface Type	(1) Display Port, (3) HDMI Ports	Power	Power Adapter	DC 24V, 3.5Amp	Characteristics	Operating Temperature	0~40°C	Storage Temperature	-20°C ~ 60°C	Operating Humidity	50% RH	Controls	Graphic OSD, Auto Adjustment	Color	Black	Audio	Yes	Adjustable Monitor Stand	Tilt	VESA	100mm x 100mm Compatible	Speakers	2 Rear Mounted (5W)	Overall Dimensions	17.5"H x 26"W x 6.75"D overall	Monitor Only Dimensions	15.5"H x 26"W x 2.35"D monitor only	Base Dimensions	11"W x 6.75"D	Weight	14.5 lbs	Carton Dimensions	28" x 20" x 6"	Shipping Weight	17 lbs	Package Contents	UPC Code	816220001495	Certifications	Energy Star	Warranty	3 year limited warranty, parts and labor	Monitor		AC Adaptor and Power Cord		HDMI Cable, Audio Cable		CD and Manual	
LCD	Panel Type	TN																																																																																					
	Visible Screen Area	28"																																																																																					
	Pixel Pitch	0.16mm x 0.016mm																																																																																					
	Max. Visible Angle	170°/160°																																																																																					
	Displayed Color	1.073 Billion Colors																																																																																					
	Response Time	5 msec (GTG)																																																																																					
	Brightness	300 cd/m²																																																																																					
	Aspect Ratio	16:9																																																																																					
	Contrast Ratio	1000:1																																																																																					
	Recommended Resolution	3840 x 2160																																																																																					
Interface	Interface	Digital																																																																																					
	Interface Type	(1) Display Port, (3) HDMI Ports																																																																																					
Power	Power Adapter	DC 24V, 3.5Amp																																																																																					
Characteristics	Operating Temperature	0~40°C																																																																																					
	Storage Temperature	-20°C ~ 60°C																																																																																					
	Operating Humidity	50% RH																																																																																					
	Controls	Graphic OSD, Auto Adjustment																																																																																					
	Color	Black																																																																																					
	Audio	Yes																																																																																					
	Adjustable Monitor Stand	Tilt																																																																																					
	VESA	100mm x 100mm Compatible																																																																																					
	Speakers	2 Rear Mounted (5W)																																																																																					
	Overall Dimensions	17.5"H x 26"W x 6.75"D overall																																																																																					
	Monitor Only Dimensions	15.5"H x 26"W x 2.35"D monitor only																																																																																					
	Base Dimensions	11"W x 6.75"D																																																																																					
	Weight	14.5 lbs																																																																																					
	Carton Dimensions	28" x 20" x 6"																																																																																					
	Shipping Weight	17 lbs																																																																																					
Package Contents	UPC Code	816220001495																																																																																					
	Certifications	Energy Star																																																																																					
	Warranty	3 year limited warranty, parts and labor																																																																																					
	Monitor																																																																																						
	AC Adaptor and Power Cord																																																																																						
	HDMI Cable, Audio Cable																																																																																						
	CD and Manual																																																																																						