

# Bluesocket 2125

Cost Effective, High Performance Dual Radio  
Outdoor 802.11ac Access Point

## Product Features

- The only 2x3:2 MIMO AP in its class with an extra receive antenna for reliability—better coverage and performance
- 802.11a/b/g/n/ac wireless access points supporting MIMO antenna technology
- Dual radio 2.4 GHz and 5 GHz
- Data rates up to 867 Mbps on 5 GHz radio and 300 Mbps on 2.4 GHz radio
- Built-in carrier class antenna and Ethernet surge protection
- Powered by 802.3at (PoE+)
- User configurable maximum-associated clients per radio
- Increased receive sensitivity to compensate for mobile devices with less transmit power
- Zero-touch AP deployment—APs automatically discover vWLAN, download firmware, and download configuration
- Supports WMM/802.11e and QoS for Enterprise-class Voice over Wi-Fi®
- DynamicRF Radio Resource Management Technology—automatically configures optimal radio settings to maximize performance
- Integrated wireless intrusion detection system to identify rogue access points and wireless attacks
- Supports stateful firewall for highest security at the edge

ADTRAN's wireless portfolio includes a family of 802.11n and 802.11ac high-performance Access Points (APs) that are a perfect fit for enterprises of all sizes, including educational institutions, retail, hospitality, and healthcare providers who are looking to move their organizations to a pervasive mobility environment. Bluesocket® APs are completely plug-and-play requiring no manual configuration and deliver optimal performance. Whether you want to add wireless to your office or deploy across an entire campus, the Bluesocket APs are designed to meet your needs.

### Cost Effective, High Performance, Reliable Connectivity

The Bluesocket 2125 outdoor 802.11ac AP offers enterprise-grade performance, with 2x3:2 MIMO, the only AP in its class with an extra receive antenna offering greater coverage, performance and reliability. The BSAP 2125 provides data rates up to 867 Mbps on the 5 GHz radio and 300 Mbps on the 2.4 GHz radio for a total of 1.2 Gbps. With a weather resistant, industrial-grade enclosure and built-in carrier class antenna and Ethernet surge protection, the BSAP 2125 APs provide the highest performance, extended range wireless coverage in the most harsh outdoor environments.

The Bluesocket 2125 APs provide cost effective, high performance, reliable coverage in medium density wireless environments with laptops, mobile phones and tablets. The BSAP 2125s offer higher receive sensitivity on both the 2.4 Ghz and 5 Ghz radios to compensate for Bring Your Own Device (BYOD) type mobile devices such as smartphones and tablets that have a fraction of the transmit power of traditional laptops.



The Bluesocket 2125 APs include six N-type connectors for external antennas, and are fully functional with power delivered by a single port 802.3at (PoE+) solution.

### Flexible, Cloud-Managed Options

The Bluesocket APs operate in conjunction with ADTRAN's flexible portfolio of cloud-managed deployment options including public cloud, private cloud or partner cloud with the freedom to migrate among them.

ADTRAN's wireless solutions are built on virtual Wirelss LAN (vWLAN), the industry's premier cloud-managed wireless LAN. ADTRAN's vWLAN® is simple yet powerful: simple in that it is intuitive, easy to learn, setup and use, and powerful with unmatched visibility, security, reliability, scalability and performance. In addition, ADTRAN's ProServices™ offers the most robust lifecycle professional services—from initial designs, to onsite surveys, to installations, all the way to end-user Help Desk.

### Deployments Made Simple—Auto Provision, Auto Configure, Auto Optimize

- **Zero-touch AP deployment:** APs automatically discover vWLAN in the cloud, download firmware and download configuration.
- **DynamicRF:** Radio Resource Management (RRM) technology maximizes performance, adapts to interference, and provides seamless L2/L3 mobility by automatically setting channel and TX power settings, discovering neighbors and load balancing.

### Unsurpassed Security, Reliability, Scalability and Performance

- **Context-aware Access Control** allows you to define security policies based on users, device type, ownership, location and schedules. Businesses can now support BYOD or allow guest access while ensuring highest levels of network security.
- **Built-in Wireless Intrusion Detection (W-IDS)** to detect and isolate rogue access points in the network.
- **Built-in High-Availability (HA)** with zero packet loss failover ensures a reliable, always-on network.
- **Elastic Scalability** allows the network to quickly scale without the constraints of legacy hardware controllers.

# Bluesocket 2125

Cost Effective, High Performance Dual Radio  
Outdoor 802.11ac Access Point

## Product Specifications

### Interfaces

- One Auto-sensing, 10/100/1000Base-T, RJ-45 Connector

### Antenna

- Six N-type Connectors

### Radios

- 802.11a/n/ac and 802.11b/g/n
- Configurable for Sensor-mode RF Scanning
- DynamicRF (Radio Resource Management) for Automatic Channel, TX Power, and Neighbor Discovery
- Configurable Maximum Associated Clients per Radio
- Multicast/Broadcast to Unicast Conversion
- A-MPDU and A-MSDU Frame Aggregation
- HT20, HT40 (High Throughput) and VHT80 (Very High Throughput)
- Max Transmit Power—400mW

### Certifications

- Wi-Fi 802.11a/b/g/n/ac Certification

### Mobility Services

- Eight SSIDs per Radio
- Support for Apple Bonjour Based Services (Airprint, Airplay), Apple CNA, and Microsoft NCSI
- Wireless Client Load Balancing
- Secure Fast Roaming with Opportunistic Key Caching (OKC)
- Seamless Layer 2 and Layer 3 Roaming
- High Availability

### QOS for Voice, Data, and Video

- Smart Bandwidth Management (Incoming, Outgoing)
- WMM (802.11e)
- 802.1p or Differentiated Service Code Point (DSCP)
- WMM Power Save (U-APSD)

### Security

- 802.1X Port-based Authentication
- Open System (WEP-64/128)
- Shared System (WEP-64/128)
- WPA/WPA2-Personal
- WPA/WPA2-Enterprise
- EAP-TTLS
- EAP-PEAP
- EAP-FAST
- EAP-TLS
- EAP-SIM
- EAP-AKA

# Bluesocket 2125

Cost Effective, High Performance Dual Radio  
Outdoor 802.11ac Access Point

## Environment

- **Operating:** -40° F to 140° F (-40° C to 55° C)
- **Storage:** -58° F to 150° F (-40° C to 70° C)
- **Humidity:** 5% to 90% Typical
- **Humidity:** 5% to 90% typical
- **Waterproof:**
  - IP67
  - Salt-spray resistant
- Built-in Carrier Class Antenna and Ethernet Surge Protection

## Physical

- **Dimensions:** 9.6 in. x 7.8 in. x 1.9 in.  
(245 mm x 200 mm x 75 mm) (L x W x H)
- **Weight:** 3.2 lbs (1.45 kg)

## Power

- 802.3at Compliant Power over Ethernet

## Mounting

- Wall/Pole/Ceiling Mount Kit Included

## Agency Approvals

Electrical/Safety Compliance

- UL 1950
- CSA 22.2
- IEC 60950
- EN 60950

## Radio Approvals

- FCC Part 15.247
- RSS-210 (Canada)
- EN 300.328 (Europe)
- AS/NZS 4771 (Australia & New Zealand)
- EMI and Susceptibility (Class A)
- FCC Part 15.107 and 15.109
- ICES-003 (Canada)
- EN 301.489-1 and -17 (Europe)
- AS/NZS 3548

## Warranty

- One Year Warranty



ADTRAN, Inc.  
Attn: Enterprise Networks  
901 Explorer Boulevard  
Huntsville, AL 35806  
P.O. Box 140000  
Huntsville, AL 35814-4000  
256 963-8000  
256 963-8699 fax

**General Information**  
800 9ADTRAN  
info@adtran.com  
www.adtran.com

**Bluesocket Business Group**  
866-633-3358  
vWLAN@adtran.com  
www.adtran.com/bluesocket

**Pre-Sales Technical Support**  
888 423-8726  
application.engineer@adtran.com  
www.adtran.com/presales

**Post-Sales Technical Support**  
888 423-8726  
www.adtran.com/supportcase

**Where to Buy**  
888 423-8726  
channel.sales@adtran.com  
www.adtran.com/where2buy

**ProServices<sup>SM</sup>**  
888 874-2237  
proservices@adtran.com  
www.adtran.com/proservices

**Training**  
888 423-8726  
training@adtran.com

**Global Inquiries**  
256 963-8000  
256 963-6300 fax  
international@adtran.com

ADTRAN believes the information in this publication to be accurate as of publication date, and is not responsible for error. Specifications subject to change without notice. ADTRAN, Bluesocket and vWLAN are registered trademarks of ADTRAN, Inc. and its affiliates in various countries. All other trademarks mentioned in this document are the property of their respective owners.

ADTRAN warranty duration and entitlements vary by product and geography. For specific warranty information, visit [www.adtran.com/warranty](http://www.adtran.com/warranty)

ADTRAN products may be subject to U.S. export controls and other trade restrictions. Any export, re-export, or transfer of the products contrary to law is prohibited. For more information regarding ADTRAN's export license, please visit [www.adtran.com/exportlicense](http://www.adtran.com/exportlicense)



TL 19.1270



ADTRAN is an ISO 9001, ISO 14001, and a TL 9000 certified supplier.

61700923F1-8A February  
Copyright © 2015 ADTRAN, Inc.  
All rights reserved.

# Bluesocket 2125

Cost Effective, High Performance Dual Radio  
Outdoor 802.11ac Access Point

## Ordering Information

### Choose Your Access Point

Choose Your AP	Part No.
<b>Outdoor AP</b>	
<b>BSAP 2125: 802.11a/b/g/n/ac, 2x3:2, External N-type Antenna Connectors</b>	<b>1700961F1</b>

### Choose Your Cloud

Public Cloud – ProCloud	Part No.	Part No.
<b>ProCloud for Outdoor AP (BSAP 2125)</b>	<b>NBD</b>	<b>7x24x4</b>
One Year	1100MSPH210112	1100MSPH310112
Three Years	1100MSPH210136	1100MSPH310136
Five Years	1100MSPH210160	1100MSPH310160

### Public Cloud – ProCloud Plus

Public Cloud – ProCloud Plus	Part No.	Part No.
<b>ProCloud Plus for Outdoor AP (BSAP 2125)</b>	<b>NBD</b>	<b>7x24x4</b>
One Year	1100MSPM210112	1100MSPM310112
Three Years	1100MSPM210136	1100MSPM310136
Five Years	1100MSPM210160	1100MSPM310160

### Private Cloud

Private Cloud	Part No.	Part No.
<b>vWLAN Virtual Appliance (VMware): <a href="http://www.adtran.com/downloadvwlan">www.adtran.com/downloadvwlan</a></b>		<b>Download Only</b>
<b>vWLAN 1U Rackmount Appliance (Hardware)</b>		<b>1700900F2</b>
<b>vWLAN Desktop Appliance (Hardware)</b>		<b>1700918F1</b>

### Licenses

Software License	Part No.
<b>Licenses purchase waived while covered by ProCloud/ProCloud Plus</b>	
<b>Access Point vWLAN Software License</b> (with built-in High Availability)	<b>1951901G1</b>
<b>Access Point Unified User Access</b> (Wired and Third-Party AP Support) <b>Software License</b> (Optional)	<b>1951910G1</b>

### Accessories

Power Supply and Antennas	Part No.
<b>802.3at compliant PoE+ injector</b> for BSAP 2125	<b>1700923F1</b>
<b>Antenna Bundle</b> for BSAP 2125	<b>1700930F1</b>