

# Bluesocket 2135

Premium, High Density, High Performance  
Dual Radio Outdoor 802.11ac Access Point

## Product Features

- 802.11a/b/g/n/ac wireless access points supporting MIMO antenna technology
- Dual radio 2.4 GHz and 5 GHz
- Full 3x3:3 MIMO performance
- Data rates up to 1.3 Gbps on 5 GHz radio and 450 Mbps on 2.4 GHz radio
- Built-in carrier class antenna and Ethernet surge protection
- Powered by 802.3at (PoE+)
- User configurable maximum-associated clients per radio
- Increased receive sensitivity to compensate for mobile devices with less transmit power
- Zero-touch AP deployment—APs automatically discover vWLAN, download firmware, and download configuration
- Supports WMM/802.11e and QoS for Enterprise-class Voice over Wi-Fi
- DynamicRF Radio Resource Management Technology—automatically configures optimal radio settings to maximise performance
- Integrated wireless intrusion detection system to identify rogue access points and wireless attacks
- Supports stateful firewall for highest security at the edge

ADTRAN's wireless portfolio includes a family of 802.11n and 802.11ac high-performance Access Points (APs) that are a perfect fit for enterprises of all sizes, including educational institutions, retail, hospitality, and healthcare providers who are looking to move their organisations to a pervasive mobility environment. Bluesocket APs are completely plug-and-play requiring no manual configuration and deliver optimal performance. Whether you want to add wireless to your office or deploy across an entire campus, the Bluesocket APs are designed to meet your needs.

### Cost Effective, High Performance, Reliable Connectivity

The Bluesocket 2135 outdoor 802.11ac AP offers enterprise-grade performance with three transmit and three receive streams providing data rates up to 1.3 Gbps on the 5 GHz radio and 450 Mbps on the 2.4 GHz radio for a total of 1.75 Gbps. With a weather resistant, industrial-grade enclosure and built-in carrier class antenna and Ethernet surge protection, the BSAP 2135 APs provide the highest performance, extended range wireless coverage in the most harsh outdoor environments.

The Bluesocket 2135 APs provide high performance, reliable coverage in ultra-high density wireless environments with laptops, mobile phones and tablets. The BSAP 2135s offer higher receive sensitivity on both the 2.4 Ghz and 5 Ghz radios to compensate for Bring Your Own Device (BYOD) type mobile devices such as smartphones and tablets that have a fraction of the transmit power of traditional laptops.

The Bluesocket 2135 APs include six N-type connectors for external antennas, and are fully functional with power delivered by a single port 802.3at (PoE+) solution.

### Flexible, Cloud-Managed Options

The Bluesocket APs operate in conjunction with ADTRAN's flexible portfolio of cloud-managed deployment options including public cloud, private cloud or partner cloud with the freedom to migrate among them.

ADTRAN's wireless solutions are built on virtual Wireless LAN (vWLAN), the industry's premier cloud-managed wireless LAN. ADTRAN's vWLAN is simple yet powerful: simple in that it is intuitive, easy to learn, setup and use, and powerful with unmatched visibility, security, reliability, scalability and performance. In addition, ADTRAN's ProServices offers the most robust lifecycle professional services—from initial designs, to onsite surveys, to installations, all the way to end-user Help Desk.

### Deployments Made Simple—Auto Provision, Auto Configure, Auto Optimise

- **Zero-touch AP deployment:** APs automatically discover vWLAN in the cloud, download firmware and download configuration.
- **DynamicRF:** Radio Resource Management (RRM) technology maximises performance, adapts to interference, and provides seamless L2/L3 mobility by automatically setting channel and TX power settings, discovering neighbors and load balancing.

### Unsurpassed Security, Reliability, Scalability and Performance

- **Context-aware Access Control** allows you to define security policies based on users, device type, ownership, location and schedules. Businesses can now support BYOD or allow guest access while ensuring highest levels of network security.
- **Built-in Wireless Intrusion Detection (W-IDS)** to detect and isolate rogue access points in the network.
- **Built-in High-Availability (HA)** with zero packet loss failover ensures a reliable, always-on network.
- **Elastic Scalability** allows the network to quickly scale without the constraints of legacy hardware controllers.



# Bluesocket 2135

Premium, High Density, High Performance  
Dual Radio Outdoor 802.11ac Access Point

## Product Specifications

### Interfaces

- One Auto-sensing, 10/100/1000Base-T, RJ-45 Connector

### Antenna

- Six N-type Connectors

### Radios

- 802.11a/n/ac and 802.11b/g/n
- Configurable for Sensor-mode RF Scanning
- DynamicRF (Radio Resource Management) for Automatic Channel, TX Power, and Neighbor Discovery
- Configurable Maximum Associated Clients per Radio
- Multicast/Broadcast to Unicast Conversion
- A-MPDU and A-MSDU Frame Aggregation
- HT20, HT40 (High Throughput) and VHT80 (Very High Throughput)
- Max Transmit Power—400mW

### Certifications

- Wi-Fi 802.11a/b/g/n/ac Certification

### Mobility Services

- Eight SSIDs per Radio
- Support for Apple Bonjour Based Services (Airprint, Airplay), Apple CNA, and Microsoft NCSI
- Wireless Client Load Balancing
- Secure Fast Roaming with Opportunistic Key Caching (OKC)
- Seamless Layer 2 and Layer 3 Roaming
- High Availability

### QoS for Voice, Data, and Video

- Smart Bandwidth Management (Incoming, Outgoing)
- WMM (802.11e)
- 802.1p or Differentiated Service Code Point (DSCP)
- WMM Power Save (U-APSD)

### Security

- 802.1X Port-based Authentication
- Open System (WEP-64/128)
- Shared System (WEP-64/128)
- WPA/WPA2-Personal
- WPA/WPA2-Enterprise
- EAP-TTLS
- EAP-PEAP
- EAP-FAST
- EAP-TLS
- EAP-SIM
- EAP-AKA

# Bluesocket 2135

Premium, High Density, High Performance  
Dual Radio Outdoor 802.11ac Access Point

## Environment

- **Operating:** -40° C to 55° C (-40° F to 140° F)
- **Storage:** -40° C to 70° C (-58° F to 150° F)
- **Humidity:** 5% to 90% typical
- **Waterproof:**
  - IP67
  - Salt-spray resistant
- Built-in Carrier Class Antenna and Ethernet Surge Protection

## Physical

- **Dimensions:** 245 mm x 200 mm x 75 mm (9.6 in. x 7.8 in. x 1.9 in.) (L x W x H)
- **Weight:** 1.45 kg (3.2 lbs)

## Power

- 802.3at Compliant Power over Ethernet

## Mounting

- Wall/Pole/Ceiling Mount Kit Included

## Agency Approvals

Electrical/Safety Compliance

- UL 1950
- CSA 22.2
- IEC 60950
- EN 60950

## Radio Approvals

- FCC Part 15.247
- RSS-210 (Canada)
- EN 300.328 (Europe)
- AS/NZS 4771 (Australia & New Zealand)
- EMI and Susceptibility (Class A)
- FCC Part 15.107 and 15.109
- ICES-003 (Canada)
- EN 301.489-1 and -17 (Europe)
- AS/NZS 3548

## Warranty

- One Year Warranty



ADTRAN, Inc.  
International Department  
U.S. Headquarters  
901 Explorer Boulevard  
Huntsville, Alabama 35806  
[www.adtran.com/global](http://www.adtran.com/global)

+1 256 963 8000  
+1 256 963 6300 fax  
[international@adtran.com](mailto:international@adtran.com)

International Customer Service  
+1 256 963 8716

Canada Headquarters—  
Toronto, Ontario  
+1 877 923 8726  
+1 905 625 2515  
[sales.canada@adtran.com](mailto:sales.canada@adtran.com)

Canada—Montreal, Quebec  
+1 877 923 8726  
+1 514 940 2888  
[sales.canada@adtran.com](mailto:sales.canada@adtran.com)

Headquarters—EMEA  
ADTRAN GmbH  
Erika-Mann-Str. 25  
80636 Munich-Germany  
+49 89 411097 111  
[sales.europe@adtran.com](mailto:sales.europe@adtran.com)

Central-/East and West Europe  
+49 89 411097 111  
[sales.cewe@adtran.com](mailto:sales.cewe@adtran.com)

South Europe  
+49 89 411097 111  
[sales.southerneurope@adtran.com](mailto:sales.southerneurope@adtran.com)

North Europe and CIS  
+49 89 411097 111  
[sales.ne@adtran.com](mailto:sales.ne@adtran.com)

Middle East and Africa  
+49 89 411097 111  
[sales.me@adtran.com](mailto:sales.me@adtran.com)

Asia  
+852 3187 7111  
[sales.asia@adtran.com](mailto:sales.asia@adtran.com)

Australia/New Zealand  
+61 3 9658 0500  
[sales.australia@adtran.com](mailto:sales.australia@adtran.com)

Mexico and Central America  
+1 256 963 3321  
+1 52 55 5280 0265 Mexico  
[sales.cala@adtran.com](mailto:sales.cala@adtran.com)

South America  
+1 256 963 3185  
[sales.brazil@adtran.com](mailto:sales.brazil@adtran.com)  
[sales.latam@adtran.com](mailto:sales.latam@adtran.com)

# Bluesocket 2135

Premium, High Density, High Performance  
Dual Radio Outdoor 802.11ac Access Point

## Ordering Information

### Choose Your Access Point

Choose Your AP	Part No.
Outdoor AP	
<b>BSAP 2135: 802.11a/b/g/n/ac, 3x3:3, External N-type Antenna Connectors</b>	<b>1700962F1</b>

### Choose Your Cloud

Public Cloud – ProCloud	Part No.	Part No.
<b>ProCloud for Outdoor AP (BSAP 2135)</b>	<b>NBD</b>	<b>7x24x4</b>
One Year	1100MSPH210112	1100MSPH310112
Three Years	1100MSPH210136	1100MSPH310136
Five Years	1100MSPH210160	1100MSPH310160

### Public Cloud – ProCloud Plus

ProCloud Plus for Outdoor AP (BSAP 2135)	Part No.	Part No.
	<b>NBD</b>	<b>7x24x4</b>
One Year	1100MSPM210112	1100MSPM310112
Three Years	1100MSPM210136	1100MSPM310136
Five Years	1100MSPM210160	1100MSPM310160

### Private Cloud

vWLAN Virtual Appliance (VMware): <a href="http://www.adtran.com/downloadvwan">www.adtran.com/downloadvwan</a>	Part No.
	<b>Download Only</b>
<b>vWLAN 1U Rackmount Appliance (Hardware)</b>	<b>1700900F2</b>
<b>vWLAN Desktop Appliance (Hardware)</b>	<b>1700918F1</b>

### Licenses

Software License	Part No.
<b>Licenses purchase waived while covered by ProCloud/ProCloud Plus</b>	
<b>Access Point vWLAN Software License (with built-in High Availability)</b>	<b>1951901G1</b>
<b>Access Point Unified User Access (Wired and Third-Party AP Support) Software License (Optional)</b>	<b>1951910G1</b>

### Accessories

Power Supply and Antennas	Part No.
<b>802.3at compliant PoE+ injector for BSAP 2135</b>	<b>1700923F1</b>
<b>Antenna Bundle for BSAP 2135</b>	<b>1700930F1</b>



TL19.1270



ADTRAN is an ISO 9001, ISO 14001, and a TL 9000 certified supplier.

**161700962F1-8A** March  
Copyright © 2015 ADTRAN, Inc.  
All rights reserved.

ADTRAN believes the information in this publication to be accurate as of publication date, and is not responsible for error. Specifications subject to change without notice. ADTRAN, Bluesocket and vWLAN are registered trademarks of ADTRAN, Inc. and its affiliates in various countries. All other trademarks mentioned in this document are the property of their respective owners.

ADTRAN warranty duration and entitlements vary by product and geography. For specific warranty information, visit [www.adtran.com/warranty](http://www.adtran.com/warranty)

ADTRAN products may be subject to U.S. export controls and other trade restrictions. Any export, re-export, or transfer of the products contrary to law is prohibited. For more information regarding ADTRAN's export license, please visit [www.adtran.com/exportlicense](http://www.adtran.com/exportlicense)