

The Chromebook with the longest battery life

- Longest battery life
- Vivid display
- Quickest connection


 Part Number: **NX.G14ED.004**

 EAN Code: **4713147969654**

 Model Name: **C810-T503**

 Country: **Nordic**

General	Type:	Chromebook
	Operating System:	Google Chrome Operating System
	2nd Operating System:	N
Processor / Chipset	CPU:	NVIDIA® Tegra® K1 mobile processor
	Core/Thread:	NVIDIA 4-Plus-1™ Quad-Core
	Frequency:	2.1 GHz
	Turbo:	2.3 GHz
	Cache:	-
	Chipset:	N/A
	Integrated Graphic Card and Gfx Base Frequency:	
Memory	RAM:	4GB DDR3 Memory
	Total memory slot	1
	Empty Slot:	0
Storage	Hard Drive:	eMMC 32GB
	2nd Hard Drive:	N/A
	Optical Drive:	N/A
Display	Panel Type:	13.3" HD LED backlit LCD Non-Glare
	Aspect Ratio:	16 : 9
	Resolution:	1366 x 768
Video / Graphic	Discrete Graphic Card:	N/A
	Camera:	Acer Crystal Eye HD webcam with 1280 x 720 resolution and 720p HD audio/video recording
	Sound:	High-definition audio support ; Two built-in stereo speakers;
Connectivity	Wireless LAN:	802.11ac Wireless LAN
	Bluetooth®:	Bluetooth® 4.0
	3G/4G:	N/A
I/O ports and Keyboard	HDMI:	Y
	VGA:	N/A
	Ethernet (RJ-45) Port:	N/A
	Acer Converter Port:	N/A
	Card reader:	SD card reader
	USB:	2 xUSB 3.0
	Audio jacks	3.5mm combo audio jack
	Backlit Keyboard:	N/A
Battery and Adaptor	Battery:	4-cell Li-Polymer battery
	2nd Battery (if available):	N/A
	AC Adaptor:	3-pin 45W AC adapter
	Battery life (Up to):	13 Hours for HD Panel, 11 Hours for FHD Panel
Dimension	Dimension:	327 (W) x 227.5 (D) x 17.95/17.95 (H) mm
	Weight (KG):	1,5
	Color (A cover):	Moonstone Black
Software and Security	Security software	TPM
	Productivity Software:	N/A
Options	Options:	N/A

• "N/A" refer to "Not Applicable"

 • Acer reserves the rights to remove products from the market or change specifications without prior notice. the text is generic for the model, variation can exist on part number level.
 • Pictures are intended simply to illustrate the product.