

Canon

 imageFORMULA
P-208

Scan-tini[®]



P-208 Personal Document Scanner

The Canon imageFORMULA P-208 Scan-tini personal document scanner's ultra-compact size and robust features make it ideal for mobile use at home, the office, and anywhere in between. It can be moved from location to location as easily as it moves paper-based information to Windows[®] and Mac[®] devices, and beyond.

Wide Variety of Uses

The P-208 scanner is ideal for stationary users and "road warriors." It provides general purpose scanning of various items, including receipts, business cards, photographs, bills, contracts, reports, letters, plastic ID cards or driver licenses, and more. Whether used at home or in the office, the device can help improve

personal efficiency, organization, and productivity. Users can benefit from its ultra-compact size and flexibility, scanning items with ease and helping reduce paper in the process.

Convenient and Portable

The P-208 scanner uses electrical power via a single USB cable connected to a computer, helping to reduce cable clutter. Slim and lightweight, the P-208 fits easily into a briefcase or bag for easy portability.

Easy Use

Upon connecting to a computer, the P-208 scanner lets users "Plug-and-Scan," without installing drivers or applications. Also, a single click can automatically adjust multiple feature settings to easily deliver the best scanned image.* The bundled Canon CaptureOnTouch software enables users to configure routine jobs for quick and easy one-touch access. It can also send scanned images directly to cloud applications, such as Evernote[™] and Microsoft[®] SharePoint[®]. This scanner is also bundled with ISIS[®] and TWAIN drivers for easy integration with third-party capture or content management systems.

Flexible Operation

The P-208 scanner is capable of scanning both sides of an item at the same time, in color or black and white. It can handle a wide variety of document types, including thick or thin documents,** and plastic or embossed cards. This scanner can also handle long documents** and detect when double-feeds occur to help ensure that no data is lost.

An optional wireless capability broadens connectivity choices. When combined with the optional WU10 Wireless Adapter and Battery Pack, the scanner not only works wirelessly in Windows and Mac environments, but also with iPad®, iPhone®, iPod touch®, and Android™ devices using the free downloadable Canon CaptureOnTouch Mobile app.



Robust Features

For maximum image quality, the P-208 scanner includes features to help improve legibility. The Auto Resolution setting is useful for scanning mixed

batches of documents and photographs, automatically adjusting the resolution to improve image quality. Other features include the ability to optimize images of scanned photographs, and Optical Character Recognition (OCR), to help convert paper-based documents into digital information that can easily be searched, stored, and shared.

Environment in Mind

The P-208 personal document scanner is part of Canon's Generation Green program. It also meets ENERGY STAR® guidelines for energy efficiency and complies with the EU RoHS and WEEE directives for reduction of hazardous substances and waste products.***

Customer Care

For investment protection, eCarePAK options are available to extend service beyond the initial one-year advanced exchange warranty period. This saves on costs associated with post-purchase maintenance and maximizes uptime throughout the product life.

Specifications

Type:	Personal Mobile Scanner
Document Feeding:	Automatic or Manual
Document Size	
Width:	2.0" - 8.5"
Length:	2.8" - 14.0"
Document Weight:	14 - 55 lb. Bond Plain Paper
Feeder Capacity:	10 Sheets
Grayscale:	8-bit
Color:	24-bit
Light Source:	RGB LED
Scanning Element:	Contact Image Sensor (CMOS)
Scanning Modes:	Color, Grayscale, Black and White
Optical Resolution:	600 dpi
Output Resolution:	150/200/300/400/600 dpi
Scanning Speeds[▲]	Simplex Duplex
Black and White:	Up to 8 ppm Up to 16 ipm
Grayscale:	Up to 8 ppm Up to 16 ipm
Color:	Up to 8 ppm Up to 16 ipm
Interface:	Hi-Speed USB 2.0
Supported OS:	Windows XP Professional (32-bit/64-bit), Windows XP Home (32-bit), Windows Vista® (32-bit/64-bit), Windows 7 (32-bit/64-bit), Windows 8 (32-bit/64-bit), Mac OS 10.5-10.7
Dimensions (H x W x D):	1.5" x 12.3" x 2.2" (with trays closed)
Weight:	1.3 lb.
Power Consumption:	2.5W or Less (Energy Saving Mode: 1.5W or Less)
Suggested Daily Volume:^{▲▲}	100 Scans
Bundled Windows Software:	ISIS/TWAIN Drivers, Canon CaptureOnTouch and CaptureOnTouch Lite (built-in), NewSoft Presto! Bizcard
Bundled Mac Software:	TWAIN Driver, Canon CaptureOnTouch and CaptureOnTouch Lite (built-in), NewSoft Presto! Bizcard

Options:	WU10 Wireless Adapter and Battery Pack, Canon CaptureOnTouch Mobile (available from the App Store or from the Google Play Store), Carrying Case, Separation Pad, eCarePAK Exchange Service
Other Features:	Auto Color Detection, Auto Page Size Detection, Auto Resolution Setting, Background Smoothing, Deskew, Edge Emphasis, Moiré Reduction, Photograph Corrections, Pre-Scan, Prevent Bleed-Through/Remove Background, Shadow Cropping, Skip Blank Page, Text Enhancement, Text Orientation Recognition, Three-Dimensional Color Correction, Double-Feed Detection, User Preferences
Item Number:	6907B007

* Scanner must be on Full Auto Mode for multiple settings to automatically adjust.

** See specifications for further detail on document type.

*** The facts and product statistics about EU RoHS and WEEE were obtained from Canon Electronics Inc. as of 2012.

▲ Examples based on typical settings, rated in pages/images per minute with letter-sized documents, portrait-feeding directions, up to 200 dpi, USB connection.

▲▲ Calculations based on scanning speed and typical daily time of use.



1-800-OK-CANON
www.usa.canon.com

Canon U.S.A., Inc.
One Canon Park
Melville, NY 11747

As an ENERGY STAR® Partner, Canon U.S.A., Inc. has certified through an independent EPA-recognized accredited laboratory that this product meets the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. CANON is a registered trademark of Canon Inc. in the United States and may also be a registered trademark or trademark in other countries. IMAGEFORMULA is a registered trademark of Canon Electronics Inc. ECAREPAK is a registered trademark of Canon U.S.A., Inc. iPad, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. All other referenced product names and marks are trademarks of their respective owners. Some items may not be available at this time, please check for availability. Specifications and availability subject to change without notice.
©2013 Canon U.S.A., Inc. All rights reserved.

