

# SPEC SHEET



## 3 FT HIGH SPEED HDMI® CABLE WITH ETHERNET

### SUPPORTS 4K AND AUDIO RETURN

- SUPPORTS UHD 4K & 2K @ 60 Hz AND 1080P
- HDMI ETHERNET CHANNEL
- DATA SPEED TRANSFER: EXCEEDS 10.2 GBPS
- AUDIO RETURN CHANNEL
- ALLOWS 3D OVER HDMI WHEN CONNECTED TO 3D DEVICES
- ADDITIONAL COLOR SPACES (sYCC601, RGB & YCC601)
- TRIPLE SHIELDED CABLE WITH COPPER SHIELDED TYPE A CONNECTORS
- CL3 RATED FOR IN WALL NON-PLENUM INSTALLATIONS



CABLE CONSTRUCTION	28 AWG
JACKET OUTER DIMENSION	7.3 MM
MINIMUM BEND RADIUS	60 MM
MAXIMUM COLOR DEPTH	48-BIT, 16 BITS PER COLOR
MAXIMUM REFRESH RATE	1080P 120 HZ SOURCE CONTENT
HDMI® HIGH SPEED	YES
ETHERNET	YES
AUDIO RETURN CHANNEL	YES
DEEP COLOR SUPPORT	YES
3D COMPATIBLE	YES
4K SUPPORT	YES
AUDIO SUPPORT	DTS, DOLBY DIGITAL
RATINGS/CERTIFICATIONS	ROHS, UL LISTED, CL3 RATED
WARRANTY	LIMITED LIFETIME

PART #: 0E-HDMI03

UPC: 811914021537

LENGTH: 3 FT.

WEIGHT: .16 LBS

Product Certification:



FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.

wboxtech.com